

NON-CATALOG

Plug-In Amplifier

AMP-2000+

50Ω Medium Power 10 to 2000 MHz


Features

- wideband, 10 to 2000 MHz
- hermetic, TO-8 can
- low noise, 5 dB typ.

Applications

- military, hi-rel applications
- VHF/UHF
- cellular
- satellite communications

"Not recommended for new designs. Please, refer to PCN# 16-004 on model's Dash Board"



CASE STYLE: QQ96

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Amplifier Electrical Specifications

MODEL NO.	FREQUENCY (MHz)		GAIN (dB)		MAXIMUM POWER (dBm)		DYNAMIC RANGE		VSWR (:1) Typ.		DC POWER	
	f_L	f_U	Min.	Flatness Max.	Output (1 dB Compr.)	Input (no damage)	NF (dB) Typ.	IP3 (dBm) Typ.	In	Out	Volt (V) Nom.	Current (mA) Max.
AMP-2000(+)	10	2000	20	±1.5	+15	+5	5.0	+25	2.0	2.0	15	100

Open load is not recommended, potentially can cause damage.
With no load derate max input power by 20 dB

Pin Connections


RF IN	5
RF OUT	11
DC	2
GROUND	1,3,4,6,7,8,9,10,12
CASE GROUND	1,3,4,6,7,8,9,10,12

Maximum Ratings

Operating Temperature	-54°C to 85°C
Storage Temperature	-55°C to 100°C
DC Voltage	+17V Max.

Permanent damage may occur if any of these limits are exceeded.

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	wt
.600	.250	.25	.016	.020	.04	.400	.200	.200	.100	grams
15.24	6.35	6.35	0.41	0.51	1.02	10.16	5.08	5.08	2.54	4.0

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp








www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

NON-CATALOG

Typical Performance Data/Curves

AMP-2000+

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR (:1)		NOISE FIGURE (dB)	POUT at 1 dB COMPR. (dBm)
	12V	15V	16V	12V	15V	16V	IN	OUT		
10.00	19.85	20.55	20.70	19.60	18.40	19.30	1.92	1.54	8.26	15.59
19.10	20.02	20.69	20.82	19.40	20.20	18.10	1.91	1.51	8.01	16.22
50.50	20.01	20.66	20.79	19.40	18.70	18.50	1.88	1.50	7.15	16.25
133.40	20.03	20.69	20.78	18.30	18.80	17.90	1.87	1.48	6.19	16.27
352.30	19.98	20.59	20.71	18.30	18.50	16.60	1.75	1.48	5.10	16.47
724.40	20.33	20.92	21.02	16.00	16.30	16.00	1.42	1.34	4.32	16.98
877.40	20.42	21.01	21.11	15.90	15.70	13.60	1.27	1.21	4.28	17.03
1030.50	20.36	20.94	21.04	14.50	14.60	14.60	1.15	1.13	4.43	17.31
1132.60	20.41	20.99	21.07	14.90	13.80	14.00	1.14	1.11	4.62	17.38
1234.60	20.36	20.93	21.03	14.20	12.90	14.20	1.19	1.15	4.64	17.41
1387.70	20.21	20.75	20.80	14.10	13.60	14.50	1.30	1.17	4.32	17.59
1540.80	20.46	20.99	21.09	13.30	12.90	13.40	1.43	1.17	4.64	17.89
1693.80	20.93	21.51	21.59	12.00	11.40	12.20	1.49	1.12	5.05	17.70
1846.90	20.93	21.61	21.76	10.70	11.10	11.70	1.38	1.03	4.51	17.26
2000.00	19.68	20.54	20.69	13.30	13.10	13.10	1.12	1.09	4.90	16.11



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

