Frequency Synthesizer DSN-2700A-1119+

2300 to 2700 MHz 50Ω

The Big Deal

- Low phase noise and spurious
- Robust design and construction



CASE STYLE: KL942

Product Overview

The DSN-2700A-1119+ is a Frequency Synthesizer, designed to operate from 2300 to 2700 MHz for Point-to-Point MW/MMW Radio application. The DSN-2700A-1119+ is packaged in a metal case (size of 1.25" x 1.00" x 0.20") to shield against unwanted signals and noise.

Key Features

Feature	Advantages
Low phase noise and spurious: • Phase Noise: -97 dBc/Hz typ. @ 10 kHz offset • Comparison Spurious: -95 dBc typ. • Reference Spurious: -96 dBc typ.	Low phase noise and spurious improve system EVM (Error Vector Magnitude).
Robust design and construction	To enhance the robustness of DSN-2700A-1119+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Frequency Synthesizer

DSN-2700A-1119+

 50Ω 2300 to 2700 MHz

Features

- Integrated VCO + PLL
- Low phase noise and spurious
- · Robust design and construction
- Low operating voltage (VCC VCO=+5V, VCC PLL=+12.5V)



CASE STYLE: KL942

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Applications

Point-to-Point MW/MMW Radio

General Description

The DSN-2700A-1119+ is a Frequency Synthesizer, designed to operate from 2300 to 2700 MHz for Pointto-Point MW/MMW Radio application. The DSN-2700A-1119+ is packaged in a metal case (size of 1.25" x 1.00" x 0.20") to shield against unwanted signals and noise. To enhance the robustness of DSN-2700A-1119+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.

Simplified Schematic



totes
Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.js

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A M151108 FDR-6825/4F1 DSN-2700A-1119+ Category-D6 RAV 151007 Page 2 of 11

Electrical Specifications (over operating temperature -33°C to +80°C)

Parameters		Test Conditions	Min.	Тур.	Max.	Units	
Frequency Range		-	2300	-	2700	MHz	
Step Size		-	-	250	-	kHz	
Settling Time		Within ± 1 kHz	-	43	-	mSec	
Output Power		-	+2.5	+6	+7.5	dBm	
		@ 100 Hz offset	-	-60	-		
		@ 1 kHz offset	-	-70	-60		
SSB Phase Noise		@ 10 kHz offset	-	-97	-90	dBc/Hz	
		@ 100 kHz offset	-	-119	-113]	
		@ 1 MHz offset	-	-139	-133		
Reference Spurious Suppress	sion	Ref. Freq. 10 MHz	-	-96	-77		
Comparison Spurious Suppre	ssion	Step Size 250 kHz	-	-95	-75	ما ال	
Non - Harmonic Spurious Sup	pression	-	-	-90	-	dBc	
Harmonic Suppression		-	-	-50	-37	1	
VCO Supply Voltage		+5.00	+4.75	+5.00	+5.25	V	
PLL Supply Voltage		+12.50	+12.25	+12.50	+12.75] V	
VCO Supply Current		-	-	39	48	Л	
PLL Supply Current		-	-	14	21	mA	
Reference Input	Frequency	10 (square wave) ensure slew rate (SR) > 50 V/μs	-	10	-	MHz	
(External)	Amplitude	1 - 1		1	-	V _{p-p}	
(External)	Input impedance	-	-	- 100 -		ΚΩ	
	Phase Noise @ 1 kHz offset	-	-	-140	-	dBc/Hz	
RF Output port Impedance		-	-	50	-	Ω	
Input Logic Lovel	Input high voltage	-	2.65	-	-	V	
Input Logic Level	Input low voltage	-	-	-	0.65	V	
Digital Look Datast	Locked	-	2.85	-	3.70	V	
Digital Lock Detect	Unlocked	-	-	-	0.40	V	
Frequency Synthesizer PLL		-	ADF4106				
PLL Programming		-	3-wire serial 3.3V CMOS				
	F_Register	-	(MSB) 100°	11111100000	00000010010	(LSB)	
Register Map @ 2700 MHz	N_Register	-	(MSB) 1000010101000101000001 (LSB)				
	R_Register	-	(MSB) 1000	0000000001	0100000 (LS	SB)	

Absolute Maximum Ratings

Parameters	Ratings
VCO Supply Voltage	5.8V
PLL Supply Voltage	14.0V
VCO Supply Voltage to PLL Supply Voltage	N.A.
Reference Frequency Voltage	0Vmin, +3.55Vmax
Data, Clock, LE Levels	0Vmin, +3.55Vmax
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

Permanent damage may occur if any of these limits are exceeded

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

FREQUENCY	PO	POWER OUTPUT			VCO CURRENT		Р	LL CUREN	IT
(MHz)		(dBm)			(mA)			(mA)	
	-38°C	+25°C	+85°C	-38°C	+25°C	+85°C	-38°C	+25°C	+85°C
2300	6.07	5.95	5.57	35.57	37.97	40.24	11.92	14.12	16.12
2306	6.03	5.91	5.54	35.59	38.00	40.26	11.91	14.12	16.12
2352	5.99	5.86	5.51	35.80	38.22	40.45	11.91	14.13	16.11
2398	6.45	6.31	5.92	35.96	38.38	40.61	11.93	14.15	16.13
2444	6.27	6.12	5.77	36.15	38.57	40.79	11.93	14.16	16.13
2490	6.52	6.31	5.92	36.27	38.72	40.93	11.92	14.15	16.13
2536	6.36	6.16	5.77	36.42	38.88	41.10	11.91	14.15	16.11
2582	6.51	6.25	5.84	36.51	38.99	41.22	11.94	14.17	16.13
2628	6.44	6.17	5.76	36.60	39.12	41.34	11.93	14.16	16.12
2674	6.17	5.89	5.50	36.70	39.22	41.46	11.92	14.15	16.11
2700	6.13	5.83	5.46	36.73	39.26	41.50	11.92	14.15	16.11

FREQUENCY	HARMONICS (dBc)							
(MHz)		F2		F3				
	-38°C	+25°C	+85°C	-38°C	+25°C	+85°C		
2300	-44.22	-44.60	-45.56	-55.64	-57.34	-57.91		
2306	-45.80	-45.76	-46.49	-56.64	-58.01	-57.69		
2352	-45.55	-45.97	-46.78	-60.55	-59.35	-58.79		
2398	-50.38	-51.31	-51.46	-62.06	-61.63	-60.44		
2444	-47.53	-48.93	-49.16	-61.06	-62.10	-60.20		
2490	-47.87	-49.53	-50.41	-66.96	-66.12	-62.90		
2536	-60.66	-61.80	-60.79	-70.10	-70.40	-66.03		
2582	-52.44	-54.97	-56.60	-67.04	-67.78	-66.64		
2628	-55.45	-63.16	-64.14	-72.70	-72.32	-73.60		
2674	-50.05	-51.78	-57.73	-72.08	-69.96	-69.49		
2700	-54.42	-56.10	-67.59	-73.83	-70.94	-71.59		

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance calculate on in this specification document are based on Mini-Circuit's applicable established test performance calculation and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Www.minicircuits.com
P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

FREQUENCY	PH	PHASE NOISE (dBc/Hz) @OFFSETS						
(MHz)	+25°C							
	100Hz	1kHz	10kHz	100kHz	1MHz			
2300	-67.21	-72.21	-96.54	-119.03	-138.80			
2306	-65.40	-71.48	-96.42	-119.11	-138.58			
2352	-66.08	-71.49	-96.43	-118.74	-139.22			
2398	-66.28	-68.56	-95.59	-118.49	-138.39			
2444	-59.79	-69.24	-95.95	-118.58	-139.03			
2490	-61.17	-68.69	-95.78	-118.41	-138.74			
2536	-61.82	-69.21	-96.77	-119.19	-139.46			
2582	-57.90	-68.17	-96.42	-119.01	-139.45			
2628	-60.43	-69.19	-96.15	-118.96	-139.39			
2674	-59.77	-69.32	-96.10	-118.62	-139.17			
2700	-58.40	-67.62	-95.97	-118.44	-138.86			

FDEOLIENCY	PHASE NOISE (dBc/Hz) @OFFSETS							
FREQUENCY (MHz)	-38°C							
	100Hz	1kHz	10kHz	100kHz	1MHz			
2300	-63.17	-71.02	-97.07	-120.84	-140.80			
2306	-63.14	-72.43	-97.35	-120.92	-140.76			
2352	-62.22	-69.76	-96.89	-120.60	-141.24			
2398	-62.55	-69.72	-96.69	-120.34	-140.49			
2444	-61.64	-67.79	-96.72	-120.38	-140.92			
2490	-60.52	-67.71	-96.72	-120.26	-140.68			
2536	-60.42	-68.20	-97.50	-120.98	-141.44			
2582	-62.08	-68.90	-97.63	-121.07	-141.64			
2628	-61.55	-68.77	-97.44	-121.02	-141.16			
2674	-60.71	-67.92	-97.63	-120.95	-141.42			
2700	-60.43	-69.30	-97.38	-120.65	-141.39			

FREQUENCY	PHASE NOISE (dBc/Hz) @OFFSETS								
(MHz)		+85°C							
. ,	100Hz	1kHz	10kHz	100kHz	1MHz				
2300	-70.21	-70.13	-95.41	-117.63	-137.64				
2306	-67.98	-70.50	-95.48	-117.54	-137.57				
2352	-66.38	-70.27	-95.15	-117.34	-137.57				
2398	-64.76	-69.56	-95.12	-117.13	-137.36				
2444	-65.52	-67.68	-95.12	-117.16	-137.54				
2490	-64.72	-68.48	-95.04	-117.11	-137.37				
2536	-64.23	-67.98	-95.57	-117.76	-137.84				
2582	-65.04	-67.60	-94.90	-117.44	-137.54				
2628	-63.11	-68.27	-94.96	-117.22	-137.56				
2674	-64.01	-66.77	-94.77	-116.82	-137.12				
2700	-64.35	-66.84	-94.49	-116.66	-136.90				

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Www.minicircuits.com

P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

COMPARISON SPURIOUS ORDER	COMPARISON SPURIOUS @Fcarrier 2300MHz+(n*Fcomparison) (dBc) note 1			COMPARISON SPURIOUS @Fcarrier 2500MHz+(n*Fcomparison) (dBc) note 1				ARISON SPU @Fcarrier Iz+(n*Fcomp (dBc) no	parison)
n	-38°C	+25°C	+85°C	-38°C	+25°C	+85°C	-38°C	+25°C	+85°C
-5	-110.52	-107.54	-112.75	-112.47	-111.30	-112.35	-113.38	-111.90	-111.83
-4	-111.52	-104.94	-112.82	-112.09	-110.39	-109.51	-111.96	-113.84	-113.85
-3	-107.57	-103.15	-109.47	-109.94	-111.87	-107.23	-112.49	-111.59	-112.00
-2	-104.21	-98.11	-106.28	-104.87	-106.75	-102.94	-104.37	-110.38	-109.13
-1	-95.74	-92.56	-97.93	-97.16	-101.33	-95.30	-93.87	-101.35	-96.08
0 ^{note 2}	-	-	-	-	-	-	-	-	-
+1	-91.03	-92.59	-99.09	-97.17	-102.50	-95.93	-95.94	-103.81	-96.47
+2	-100.38	-98.83	-106.29	-103.57	-105.92	-103.25	-106.53	-109.50	-109.90
+3	-106.60	-102.82	-107.49	-109.96	-107.62	-107.74	-111.03	-111.49	-111.55
+4	-111.45	-106.49	-111.26	-113.34	-110.06	-111.66	-112.62	-112.38	-113.96
+5	-110.68	-107.08	-113.14	-112.86	-113.36	-113.81	-114.05	-113.19	-111.91

Note 1: Comparison frequency 250 kHz

Note 2: All spurs are referenced to carrier signal (n=0).


REFERENCE SPURIOUS ORDER	REFERENCE SPURIOUS @Fcarrier 2300MHz+(n*Freference) (dBc) note 3			REFERENCE SPURIOUS @ Fcarrier 2500MHz+(n*Freference) (dBc) note 3			RENCE SPU @Fcarrier Hz+(n*Frefe (dBc)	erence)	
n	-38°C	+25°C	+85°C	-38°C	+25°C	+85°C	-38°C	+25°C	+85°C
-5	-131.64	-128.45	-129.01	-129.21	-130.20	-129.85	-125.64	-129.83	-130.79
-4	-131.17	-129.92	-132.14	-129.89	-127.95	-132.16	-127.48	-121.26	-130.47
-3	-131.44	-130.04	-129.34	-131.73	-129.07	-125.62	-125.54	-127.00	-128.17
-2	-108.14	-109.31	-108.82	-108.28	-108.88	-108.52	-108.11	-105.01	-107.78
-1	-97.43	-96.77	-97.31	-97.49	-96.49	-96.73	-97.96	-92.20	-97.06
o ^{note 4}	-	-	-	-	-	-	-	-	-
+1	-97.67	-95.30	-96.90	-97.97	-97.04	-96.81	-97.81	-94.99	-96.19
+2	-108.93	-109.15	-109.51	-109.55	-108.68	-108.57	-108.84	-111.08	-110.36
+3	-129.54	-124.30	-129.17	-130.55	-125.25	-130.24	-132.21	-126.02	-125.81
+4	-131.07	-127.60	-129.87	-128.11	-132.43	-130.18	-129.19	-125.31	-130.63
+5	-131.79	-129.45	-131.76	-129.54	-126.04	-131.86	-130.07	-125.85	-128.21


Note 3: Reference frequency 10 MHz


Note 4: All spurs are referenced to carrier signal (n=0).

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Curves











Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


Mini-Circuits















Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


Mini-Circuits















Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits

Pin Configuration




Pin Connection


Pin Number	Function	Pin Number	Function
1	GND	12	LE
2	GND	13	GND
3	GND	14	REF IN
4	GND	15	GND
5	RF OUT	16	VCC VCO
6	GND	17	GND
7	LOCK DET	18	VCC PLL
8	GND	19	GND
9	DATA	20	GND
10	GND	21	GND
11	CLOCK	22	GND

Recommended Application Circuit

Note: REF IN and RF OUT ports are internally AC coupled.



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

Case Style: KL942

Tape & Reel: TR-F97

Suggested Layout for PCB Design: PL-318

Evaluation Board: TB-553+

Environment Ratings: ENV03T2

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp