Ceramic Bandpass Filter

50Ω 3000 to 4600 MHz

The Big Deal

- LTCC construction
- Temperature stable from -55 to +100°C
- Small size (0.126 x .063 X .037")

BFCN-3700+



Product Overview

The BFCN-3700+ LTCC bandpass filter covers the 3000 to 4600 MHz passband with 1.9 dB passband insertion loss and 28 dB lower stopband rejection, and 24 dB upper stopband rejection. This model handles up to 2.5W RF input power and provides a wide operating temperature range from -55 to +100°C. Utilizing LTCC multi-layer construction, the filter achieves excellent repeatability of performance and comes in a tiny 1206 ceramic package with wraparound terminations, minimizing performance variations due to parasitics and saving space in dense PCB layouts.

Key Features

Feature	Advantages				
LTCC Construction	Provides a rugged package well suited for tough environments such as high humidity and temperature extremes.				
Tiny size (0.126 x .063 x .037")	Saves space in dense circuit boards and minimizes the effects of parasitics.				
Wrap-around terminations	Provides excellent solderability and easy visual inspection				
Wide operating temperature range, -55 to +100°C	Enables reliable performance in extreme environments				

Ceramic Bandpass Filter

50Ω 3000 to 4600 MHz

Features

- Small size(0.126 x .063 x .037)
- Temperature stable
- LTCC construction

Applications

- Harmonic rejection
- Transmitters / Receivers





Generic photo used for illustration purposes only

CASE STYLE: FV1206-4

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

 Available Tape and Reel at no extra cost


 Reel Size
 Devices/Reel


 7"
 20, 50, 100, 200, 500, 1000, 3000

Specification Definition



Functional Schematic





Pad Connections

1

з


2.4


Input


Output


Ground

BFCN-3700+ INSERTION LOSS (Full Band)









REV. A ECO-011185 ED-17088 BFCN-3700+ AVB/CP/AM 211221 Page 2 of 3

⊒Mini-Circuits⁰

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Electrical Specifications^{1,2} at 25°C

Parameter		F# Frequency (MHz)		Min.	Тур.	Max.	Unit
	Center Frequency	—			3700		MHz
Pass Band	Insertion Loss	F1 - F2	3000 - 4600	—	1.9	3.5	dB
	VSWR	F1 - F2	3000 - 4600	_	2.26	—	:1
Step Band Lawer	Insertion Loss	DC - F3	2100	21	28	—	dB
Stop Band, Lower	VSWR	DC - F3	2100	_	23	—	:1
Stop Band, Upper	Insertion Loss	F4 - F5	5600 - 8000	10	24	_	dB
Stop Ballu, Opper	VSWR	F4 - F5	5600 - 8000	_	16	—	:1

1. Measured on Mini-Circuits Characterization Test Board TB-824+.

2. This filter is not intended for use as a DC Blocking circuit element. In Application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port.

Maximum Ratings

Operating Temperature	-55°C to +100°C				
Storage Temperature	-55°C to +100°C				
RF Power Input*	2.5 W at 25°C				

Passband rating, derate linearly to 0.7 W at 100°C ambient Permanent damage may occur if any of these limits are exceeded.

Bandpass Filter

BFCN-3700+


Ful	I Band Performar	nce	Pass Band Performance				
Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Insertion Loss (dB)	Group Delay (nsec)		
10	52.11	164.39	3000	1.47	0.61		
40	86.34	64.21	3100	1.25	0.53		
100	70.07	63.01	3200	1.22	0.47		
1000	35.19	45.24	3300	1.26	0.42		
1500	30.86	41.09	3400	1.34	0.39		
2100	41.10	34.12	3500	1.43	0.36		
2500	12.46	15.28	3600	1.53	0.35		
3000	1.47	1.47	3700	1.64	0.34		
3800	1.73	2.16	3800	1.73	0.33		
4600	2.10	2.01	3900	1.84	0.33		
5400	22.42	16.29	4000	1.92	0.33		
6000	29.18	26.35	4100	2.00	0.33		
6700	27.04	24.76	4250	2.08	0.35		
7300	25.18	14.98	4400	2.11	0.39		
8000	30.58	4.62	4600	2.10	0.46		

Pad Connections

Input	1
Output	3
Ground	2,4


Product Marking: GP

Outline Drawing



A .126 3.20		.037	.026	.075	F .012 0.30	.182	.104	.069
К .119 3.02	.041	.039	N .013 0.33	.024	_	R .039 0.99		wt grams .020

Demo Board MCL P/N: TB-824+ Suggested PCB Layout (PL-454)



 INDIES:
 INTRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .0066°±.0007°. COPPER: 1/2 02. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.

 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBE (SOLDER MASK.

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com