

## Non-Catalog Model

# RF Transformer

# FT1.22-1

Impedance Ratio : 1.22

### Important Note

This is a non-catalog model and can be manufactured on specific request.  
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : H16

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		0.005		100	MHz
Insertion Loss *	3 dB Bandwidth		0.005 - 100		MHz
	2 dB Bandwidth		0.01 - 50		MHz
	1 dB Bandwidth		0.05 - 25		MHz

### Notes:

\* Insertion Loss is referenced to mid-band loss, 0.08dB typ.

Impedance Ratio = Secondary / Primary

### Configuration : D

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA

