## Ceramic

# **Bandpass Filter**

#### 4700 to 6000 MHz $50\Omega$

#### **Features**

- Wide passband, 4700-6000 MHz
- Low loss, 1.3 dB typ.
- Small size 0603(1.6 x 0.8 mm)
- Temperature stable
- LTCC construction

### **Applications**

- Wireless communication (ISM)
- Harmonic Rejection
- Transmitters / receivers

## **BFCW-542+**




CASE STYLE:JC0603C-1


#### +RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




#### **Specification Definition**







## **Top View**



#### **Pad Connections**

Input	1
Output	3
Ground	2,4

## Electrical Specifications<sup>1,2</sup> at 25°C

Parar	meter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	_			5350		MHz
Pass Band	Insertion Loss	F1 - F2	4700 - 6000	_	1.3	1.8	dB
	VSWR	F1 - F2	4700 - 6000	_	1.5	2.0	:1
Stop Band, Lower	Insertion Loss	DC - F3	DC - 2500	30	34		dB
Stop Band, Upper	Insertion Loss	F4 - F5	9800 - 12000	26	34	_	dB


- 1. Measured on Mini-Circuits Characterization Test Board TB-720+.
- 2. This filter is not intended for use as a DC Blocking circuit element. In Application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port.


#### **Maximum Ratings**


Operating Temperature	-55°C to +100°C
Storage Temperature*	-55°C to +100°C
RF Power Input**	1W at 25°C

\* 12 months max.

\*\*Passband rating, derate linearly to 0.5W at 100°C ambient Permanent damage may occur if any of these limits are exceeded.







#### **Full Band Performance**


#### **Pass Band Performance**

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	77.28	508.40	4500	1.74	1.61
100	57.45	289.52	4600	1.51	1.45
500	44.18	127.06	4700	1.35	1.35
1000	38.54	85.51	4800	1.26	1.29
2500	39.92	55.73	4900	1.19	1.27
3300	21.56	31.19	5000	1.16	1.28
4200	3.47	2.94	5100	1.14	1.29
4700	1.35	1.35	5200	1.12	1.30
5000	1.16	1.28	5400	1.12	1.32
6000	1.34	1.13	5500	1.13	1.31
6800	3.36	2.06	5600	1.15	1.30
8000	28.56	17.19	5700	1.18	1.26
9800	33.73	23.08	5800	1.21	1.22
11000	36.32	20.32	5900	1.26	1.14
12000	37.56	25.90	6000	1.34	1.13

#### **Pad Connections**


Input	1
Output	3
Ground	2,4

#### **Outline Drawing**



#### A .063 G H .100 .071 .031 .024 .018 .028 .006 .012 0.61 0.46 0.71 0.15 0.30 1.80 .032 .012 .028 .049 .026 .016 .014 arams 0.71 0.30 0.41 0.36 0.005

#### Demo Board MCL P/N: TB-720+ Suggested PCB Layout (PL-412)



#### NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC
  THICKNESS .010" ± .001". COPPER: 1/2 0Z. EACH SIDE. FOR OTHER
  MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
   BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
  - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

#### **Additional Notes**

Outline Dimensions (inch )

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

