DBTC-9-4X+

5 to 1000 MHz 9dB coupling, 50Ω .

Features

- · very flat coupling
- · very broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- · leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521



Generic photo used for illustration purposes only CASE STYLE: AT1667-1

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Applications

- VHF/UHF receivers/transmitters
- cellular

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range		5		1000	MHz	
	5-50		1.2	2.0		
Mainline Loss	50-500		1.2	1.8	dB	
	500-1000		1.5	2.0		
Nominal Coupling	5-1000		9.0±0.5		dB	
Coupling Flatness(±)	5-1000			±0.5	dB	
	5-50	17	21			
Directivity	50-500	13	18		dB	
•	500-1000	_	15			
VSWR	5-1000		1.2		dB	
	5-50			0.5		
Input Power	50-500			1.0	W	
	500-1000			1.0		

^{1.} Includes theoretical coupled power loss of 0.58 dB at 9 dB coupling 2. For coupled port VSWR above 500 MHz, 1.6:1 typ.

Maximum Ratings

Parameter	Ratings		
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

Function	Pin Number		
INPUT	3		
OUTPUT	4		
COUPLED	1		
GROUND	2		
ISOLATE (DO NOT USE)	6		

Product Marking




Electrical Schematic





Demo Board MCL P/N: TB-278

Outline Drawing



Suggested PCB Layout (PL-150) 4X \$0.015 PTH FOR GROUND -45° TYP -013 TYP PACKAGE OUTLINE .050, 2 PL. -044 TRACE WIDTH, 3 PL. (SEE NOTE BELOW) WIDTH IS SHOWN FOR ROGERS RO4350R WITH DIFFER

NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)


DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK


Outline Dimensions (inch)


· · · · · · ·					
F	E	D	С	В	Α
.025	.030	.050	.150	.150	.150
0.64	0.76	1.27	3.81	3.81	3.81
wt		K	J	Н	G
grams		.030	.160	.050	.028
0.10		0.76	4.06	1.27	0.71

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)	Directivity (dB)	Return Loss (dB)		
	In-Out	In-CpI	(/	In	Out	Cpl
5.00	1.18	8.93	21.62	17.90	24.67	18.40
10.00	1.10	8.89	21.70	19.15	29.04	19.50
50.00	1.07	8.87	21.50	20.07	32.70	20.22
100.00	1.09	8.90	20.99	20.12	31.81	20.27
300.00	1.16	8.93	19.47	20.49	30.43	18.93
500.00	1.20	8.90	17.60	21.02	30.62	16.66
600.00	1.23	8.88	16.50	20.89	30.39	15.36
800.00	1.31	8.86	14.74	20.45	30.31	12.91
900.00	1.37	8.85	14.07	20.06	29.26	11.86
1000.00	1.43	8.86	13.44	19.34	27.16	10.86







Additional Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp