

Non-Catalog Model

Frequency Mixer

GRA-6H

Level 17 (LO Power +17 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : D09


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	0.01		50	MHz
	RF (fL to fU)	0.01		50	MHz
	IF	0		50	MHz
Conversion Loss	mid band		5.0	6.0	dB
	Total Range			7.0	dB
LO-RF Isolation	Low Range	45	50		dB
	Mid Range	30	45		dB
	Upper Range	25	35		dB
LO-IF Isolation	Low Range	40	50		dB
	Mid Range	35	47		dB
	Upper Range	25	32		dB
IP3 Input		+27.5	+30		dBm
1 dB Comp. Input Power			+10		dBm

Notes: Low Range = [fL to 10fL] Mid Range = [10fL to fU/2] Upper Range = [fU/2 to fU]
 mid band = [2fL to fU/2]

IP3 : RF Power = 0 dBm @ 200 MHz & 202 MHz , LO Power = +17 dBm @ 180 MHz

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA

Electrical Schematics



PIN CONNECTIONS	
LO	1
RF	6
IF	4
GROUND	2, 3, 5