

# Coaxial Fixed Attenuator

## HAT-30+

50Ω 1W 30dB DC to 2000 MHz

### Maximum Ratings

Operating Temperature	-45°C to 100°C
Storage Temperature	-55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

### Features

- excellent VSWR, 1.05:1 typ.
- excellent flatness, 0.80 dB typ. to 2000 MHz
- usable to 4000 MHz



Generic photo used for illustration purposes only

CASE STYLE: FF747

Connectors	Model
BNC Male-BNC Female	HAT-30+


### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Applications

- PCS
- instrumentation
- cellular

### Outline Drawing



### Outline Dimensions (inch/mm)

B	D	wt
.62	1.94	grams
15.75	49.28	30.0

### Electrical Specifications




FREQ. RANGE (MHz)	ATTENUATION (dB)					VSWR (:1)			MAX. INPUT POWER (W)
	Flatness*					DC-0.5 GHz	DC-1 GHz	DC-2 GHz	
	Nom.	DC-0.5 GHz Typ.	DC-1 GHz Typ.	DC-2 GHz Typ.	Total Band Typ.				
DC-2000	30±0.2	0.30	0.60	0.80	1.30	1.05	1.10	1.15	1.0

\* Flatness = variation over band divided by 2.

### Typical Performance Data

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
10.00	29.98	1.00
50.00	29.98	1.00
100.00	30.00	1.01
250.00	29.97	1.01
500.00	29.80	1.01
750.00	29.69	1.03
1000.00	29.74	1.04
1500.00	29.86	1.08
1750.00	30.02	1.09
2000.00	30.17	1.11

### Electrical Schematic



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

