

# Frequency Synthesizer

KSN-2025A+

50Ω 2010 to 2025 MHz

## The Big Deal

- Fractional N synthesizer
- Low phase noise and spurious
- Robust design and construction
- Small size 0.80" x 0.58" x 0.15"



CASE STYLE: DK801

## Product Overview

The KSN-2025A+ is a Frequency Synthesizer, designed to operate from 2010 to 2025 MHz for TD-SCDMA application. The KSN-2025A+ is packaged in a metal case (size of 0.80" x 0.58" x 0.15") to shield against unwanted signals and noise.

## Key Features

Feature	Advantages
Low phase noise and spurious: <ul style="list-style-type: none"><li>• Phase Noise: -98 dBc/Hz typ. @ 10 kHz offset</li><li>• Step Size Spurious: -88 dBc typ.</li><li>• Comparison Spurious: -85 dBc typ.</li><li>• Reference Spurious: -88 dBc typ.</li></ul>	Low phase noise and spurious improve system EVM (Error Vector Magnitude).
Robust design and construction	To enhance the robustness of KSN-2025A+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.
Small size, 0.80" x 0.58" x 0.15"	The small size enables the KSN-2025A+ to be used in compact designs.

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)

Surface Mount

# Frequency Synthesizer

KSN-2025A+

50Ω 2010 to 2025 MHz

## Features

- Fractional N synthesizer
- Integrated VCO + PLL
- Low phase noise and spurious
- Robust design and construction
- Low operating voltage (VCC VCO=+5V, VCC PLL=+3V)
- Small size 0.80" x 0.58" x 0.15"



CASE STYLE: DK801

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


## Applications

- TD-SCDMA

## General Description

The KSN-2025A+ is a Frequency Synthesizer, designed to operate from 2010 to 2025 MHz for TD-SCDMA application. The KSN-2025A+ is packaged in a metal case (size of 0.80" x 0.58" x 0.15") to shield against unwanted signals and noise. To enhance the robustness of KSN-2025A+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.

## Simplified Schematic



### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B  
M151108  
EDR-8991F1  
KSN-2025A+  
Category-A1  
RAV  
151007  
Page 2 of 12

**Electrical Specifications** (over operating temperature -40°C to +85°C)

Parameters		Test Conditions	Min.	Typ.	Max.	Units
Frequency Range		-	2010	-	2025	MHz
Step Size		-	-	40	-	kHz
Comparison Frequency		-	-	20.48	-	MHz
Settling Time		Within $\pm 1$ kHz	-	5	-	mSec
Output Power		-	+1	+4	+7	dBm
SSB Phase Noise	@ 100 Hz offset	-	-	-75	-	dBc/Hz
	@ 1 kHz offset	-	-	-85	-79	
	@ 10 kHz offset	-	-	-98	-90	
	@ 100 kHz offset	-	-	-127	-120	
	@ 1 MHz offset	-	-	-147	-140	
Integrated SSB Phase Noise		@ 10 Hz to 1 MHz	-	-44	-36	dBc
Step Size Spurious Suppression		Step Size 40 kHz	-	-88	-65	dBc
0.5 Step Size Spurious Suppression		0.5 Step Size 20 kHz	-	-80	-62	
Reference Spurious Suppression		Ref. Freq. 61.44 MHz	-	-88	-70	
Comparison Spurious Suppression		Comp. Freq. 20.48 MHz	-	-85	-70	
Non - Harmonic Spurious Suppression		-	-	-90	-	
Harmonic Suppression		-	-	-26	-20	V
VCO Supply Voltage		+5.00	+4.75	+5.00	+5.25	
PLL Supply Voltage		+3.00	+2.85	+3.00	+3.15	mA
VCO Supply Current		-	-	46	53	
PLL Supply Current		-	-	16	25	
Reference Input (External)	Frequency	61.44 (square wave)	-	61.44	-	MHz
	Amplitude	1	-	1	-	V <sub>P-P</sub>
	Input impedance	-	-	100	-	K $\Omega$
	Phase Noise @ 1 kHz offset	-	-	-135	-	dBc/Hz
RF Output port Impedance		-	-	50	-	$\Omega$
Input Logic Level	Input high voltage	-	2.55	-	-	V
	Input low voltage	-	-	-	0.55	V
Digital Lock Detect	Locked	-	2.45	-	3.15	V
	Unlocked	-	-	-	0.40	V
Frequency Synthesizer PLL		-	ADF4153			
PLL Programming		-	3-wire serial 3V CMOS			
Register Map @ 2025 MHz	R0_Register	-	(MSB) 000110001000011100000100 (LSB)			
	R1_Register	-	(MSB) 0001010011001000000000001 (LSB)			
	R2_Register	-	(MSB) 000000000000000111000010 (LSB)			
	R3_Register	-	(MSB) 0000000000000000000000011 (LSB)			

**Absolute Maximum Ratings**

Parameters	Ratings
VCO Supply Voltage	5.8V
PLL Supply Voltage	4.0V
VCO Supply Voltage to PLL Supply Voltage	-0.3V to +5.8V
Reference Frequency Voltage	-0.3Vmin, VCC PLL +0.3Vmax
Data, Clock, LE Levels	-0.3Vmin, VCC PLL +0.3Vmax
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

Permanent damage may occur if any of these limits are exceeded

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Typical Performance Data

FREQUENCY (MHz)	POWER OUTPUT			VCO CURRENT			PLL CURENT		
	(dBm)			(mA)			(mA)		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
2010	4.09	4.30	4.34	44.42	45.81	47.23	14.32	16.25	19.10
2013	4.11	4.29	4.34	44.48	45.82	47.23	14.29	16.22	19.08
2016	4.12	4.30	4.34	44.50	45.83	47.23	14.17	16.11	18.96
2019	4.12	4.30	4.34	44.51	45.84	47.23	14.09	16.03	18.87
2022	4.14	4.31	4.34	44.51	45.84	47.23	14.08	16.02	18.87
2025	4.14	4.32	4.34	44.50	45.84	47.23	14.16	16.11	18.97

FREQUENCY (MHz)	HARMONICS (dBc)					
	F2			F3		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
2010	-25.66	-28.20	-31.18	-23.99	-25.80	-29.67
2013	-25.85	-28.43	-31.56	-23.87	-25.73	-29.70
2016	-26.13	-28.73	-31.70	-23.83	-25.67	-29.68
2019	-26.46	-29.10	-31.87	-23.92	-25.68	-29.72
2022	-26.86	-29.54	-32.18	-24.22	-25.83	-29.87
2025	-27.26	-29.88	-32.50	-24.56	-26.13	-30.17

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @ OFFSETS				
	+25°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
2010	-80.78	-85.34	-97.33	-126.77	-146.96
2013	-80.68	-86.00	-97.86	-126.79	-147.10
2016	-80.56	-85.77	-97.71	-126.68	-146.98
2019	-80.46	-85.53	-97.53	-126.59	-146.88
2022	-80.39	-85.51	-97.53	-126.56	-146.90
2025	-82.07	-86.64	-97.56	-126.54	-146.86

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @ OFFSETS				
	-45°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
2010	-75.95	-83.54	-93.07	-127.60	-148.11
2013	-77.76	-82.43	-93.70	-127.65	-148.11
2016	-79.56	-83.07	-93.28	-127.71	-148.08
2019	-80.05	-83.42	-93.08	-127.70	-148.01
2022	-78.21	-82.74	-93.62	-127.57	-147.90
2025	-77.56	-83.07	-93.64	-127.60	-148.08

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @ OFFSETS				
	+85°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
2010	-77.76	-87.31	-97.43	-125.26	-145.51
2013	-78.75	-87.95	-98.28	-125.16	-145.34
2016	-78.93	-86.79	-98.13	-125.08	-145.32
2019	-78.68	-86.00	-97.92	-124.99	-145.33
2022	-77.94	-86.41	-97.88	-124.87	-145.35
2025	-79.40	-88.11	-97.92	-124.94	-145.13

Notes  
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



COMPARISON SPURIOUS ORDER	COMPARISON SPURIOUS @Fcarrier 2010MHz+(n*Fcomparison) (dBc) note 1			COMPARISON SPURIOUS @Fcarrier 2018MHz+(n*Fcomparison) (dBc) note 1			COMPARISON SPURIOUS @Fcarrier 2025MHz+(n*Fcomparison) (dBc) note 1		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
-5	-81.22	-81.33	-80.88	-81.48	-81.15	-79.78	-83.18	-82.61	-80.60
-4	-86.52	-86.47	-90.50	-86.32	-86.49	-89.29	-87.89	-88.24	-89.99
-3	-94.71	-90.41	-92.88	-96.20	-90.38	-92.30	-97.05	-91.63	-91.88
-2	-96.76	-96.90	-99.44	-95.28	-96.54	-101.43	-94.34	-96.32	-104.72
-1	-90.13	-94.95	-94.58	-90.10	-96.03	-96.62	-90.62	-97.28	-97.68
0 <sup>note 2</sup>	-	-	-	-	-	-	-	-	-
+1	-91.56	-98.63	-97.99	-90.52	-100.87	-97.94	-90.35	-103.88	-96.29
+2	-93.15	-98.48	-95.27	-93.53	-100.22	-93.68	-94.75	-103.40	-93.76
+3	-94.61	-99.57	-100.40	-92.87	-97.91	-98.17	-93.78	-99.79	-98.39
+4	-90.14	-90.45	-87.23	-88.71	-88.52	-86.27	-89.31	-89.17	-87.57
+5	-82.27	-81.38	-82.42	-81.72	-80.82	-81.18	-82.89	-82.14	-82.17

Note 1: Comparison frequency 20.48 MHz

Note 2: All spurs are referenced to carrier signal (n=0).

REFERENCE SPURIOUS ORDER	REFERENCE SPURIOUS @Fcarrier 2010MHz+(n*Freference) (dBc) note 3			REFERENCE SPURIOUS @Fcarrier 2018MHz+(n*Freference) (dBc) note 3			REFERENCE SPURIOUS @Fcarrier 2025MHz+(n*Freference) (dBc) note 3		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
-5	-93.90	-91.35	-92.98	-99.55	-92.91	-98.85	-106.97	-94.89	-106.25
-4	-89.54	-92.53	-86.49	-88.79	-90.97	-86.66	-88.49	-89.68	-88.88
-3	-94.37	-91.92	-89.10	-91.78	-89.21	-89.33	-92.43	-89.33	-91.71
-2	-78.54	-80.02	-83.69	-77.48	-79.13	-83.40	-77.53	-79.30	-84.02
-1	-93.95	-90.41	-92.67	-96.15	-90.25	-92.67	-97.60	-91.64	-91.86
0 <sup>note 4</sup>	-	-	-	-	-	-	-	-	-
+1	-94.21	-99.25	-102.28	-93.17	-97.96	-98.05	-93.92	-99.46	-98.71
+2	-79.36	-81.61	-84.96	-78.85	-80.72	-84.50	-79.64	-81.47	-85.14
+3	-107.02	-98.57	-94.21	-105.09	-96.80	-94.46	-104.07	-99.01	-95.96
+4	-91.06	-86.07	-86.22	-92.63	-85.90	-85.95	-93.86	-86.35	-85.83
+5	-102.07	-97.44	-97.55	-106.32	-95.79	-96.52	-101.71	-94.51	-95.90

Note 3: Reference frequency 61.44 MHz

Note 4: All spurs are referenced to carrier signal (n=0).

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)






STEP SIZE SPURIOUS ORDER	0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 2010MHz+(n*Fstep size) (dBc) note 5			0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 2018MHz+(n*Fstep size) (dBc) note 5			0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 2025MHz+(n*Fstep size) (dBc) note 5		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
n									
-5.0	-94.99	-97.96	-95.73	-97.25	-93.43	-95.58	-92.20	-97.52	-93.20
-4.5	-95.93	-91.92	-92.80	-90.64	-95.72	-92.16	-94.88	-93.19	-90.98
-4.0	-89.88	-90.89	-94.54	-87.71	-93.17	-90.64	-93.68	-89.07	-92.57
-3.5	-90.47	-87.73	-86.91	-92.55	-90.95	-91.48	-91.75	-89.90	-90.60
-3.0	-84.37	-85.91	-89.24	-88.66	-89.08	-88.51	-87.39	-87.94	-89.95
-2.5	-82.25	-88.32	-84.89	-81.88	-81.90	-84.76	-81.98	-82.07	-85.90
-2.0	-85.17	-87.02	-87.30	-88.55	-85.99	-85.82	-82.07	-87.58	-85.85
-1.5	-84.44	-82.04	-84.13	-84.83	-85.68	-87.36	-80.04	-87.03	-86.23
-1.0	-86.25	-84.96	-82.64	-83.72	-87.14	-87.44	-87.24	-85.13	-85.63
-0.5	-70.12	-74.48	-71.88	-69.53	-75.85	-75.31	-72.56	-75.92	-75.04
0 <sup>note 6</sup>	-	-	-	-	-	-	-	-	-
+0.5	-70.84	-73.94	-72.00	-69.38	-75.75	-76.57	-71.94	-75.87	-73.43
+1.0	-87.38	-82.05	-85.35	-86.34	-85.82	-84.44	-81.44	-86.52	-85.56
+1.5	-80.03	-79.53	-84.32	-86.42	-84.52	-85.17	-86.55	-83.47	-88.19
+2.0	-86.33	-83.83	-84.82	-85.93	-86.23	-87.35	-84.39	-86.07	-86.72
+2.5	-86.47	-87.71	-87.05	-88.36	-86.51	-86.14	-86.53	-83.78	-86.57
+3.0	-88.94	-87.16	-85.25	-86.87	-85.53	-88.15	-89.78	-86.84	-86.35
+3.5	-89.32	-91.81	-91.42	-91.62	-91.78	-90.31	-90.94	-85.55	-88.63
+4.0	-90.01	-94.63	-87.56	-88.86	-93.38	-91.77	-93.72	-94.64	-93.25
+4.5	-93.62	-93.09	-90.11	-94.31	-96.23	-93.66	-94.94	-94.43	-91.98
+5.0	-97.59	-94.86	-95.25	-94.62	-96.75	-94.57	-97.49	-98.04	-93.76






Note 5: Step size 40 kHz  
Note 6: All spurs are referenced to carrier signal (n=0).

Notes  
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

Typical Performance Curves









Notes  
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)






Notes  
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)






Notes  
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)





Notes  
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

Pin Configuration




Pin Connection

Pin Number	Function
1	VCC PLL
2	GND
3	REF IN
4	GND
5	VCC VCO
6	GND
7	RF OUT
8	GND
9	LOCK DET
10	CLOCK
11	DATA
12	LE
13	GND
14	GND

Recommended Application Circuit


Note: REF IN and RF OUT ports are internally AC coupled.



Notes  
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Device Marking



### Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

**Case Style:** DK801

**Tape & Reel:** TR-F28

**Suggested Layout for PCB Design:** PL-249

**Evaluation Board:** TB-567-2+

**Environment Ratings:** ENV03T2

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)