

Frequency Synthesizer

KSN-1050A-119+

50Ω 970 to 1050 MHz

The Big Deal

- Low phase noise and spurious
- Robust design and construction
- Small size 0.800" x 0.584" x 0.154"



CASE STYLE: DK1042

Product Overview

The KSN-1050A-119+ is a Frequency Synthesizer, designed to operate from 970 to 1050 MHz for W-CDMA base station application. The KSN-1050A-119+ is packaged in a metal case (size of 0.800" x 0.584" x 0.154") to shield against unwanted signals and noise.

Key Features

Feature	Advantages
Low phase noise and spurious: <ul style="list-style-type: none"> • Phase Noise: -94 dBc/Hz typ. @ 10 kHz offset • Comparison Spurious: -83 dBc typ. • Reference Spurious: -103 dBc typ. 	Low phase noise and spurious improve system EVM (Error Vector Magnitude).
Robust design and construction	To enhance the robustness of KSN-1050A-119+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.
Small size, 0.800" x 0.584" x 0.154"	The small size enables the KSN-1050A-119+ to be used in compact designs.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



50Ω 970 to 1050 MHz

Features

- Integrated VCO + PLL
- Low phase noise and spurious
- Robust design and construction
- Low operating voltage (VCC VCO=+5V, VCC PLL=+5V)
- Small size 0.800" x 0.584" x 0.154"



CASE STYLE: DK1042

+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix has been added in order to identify RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.


Applications

- W-CDMA base station

General Description

The KSN-1050A-119+ is a Frequency Synthesizer, designed to operate from 970 to 1050 MHz for W-CDMA base station application. The KSN-1050A-119+ is packaged in a metal case (size of 0.800" x 0.584" x 0.154") to shield against unwanted signals and noise. To enhance the robustness of KSN-1050A-119+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.

Simplified Schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Electrical Specifications *(over operating temperature -40°C to +85°C)*

Parameters		Test Conditions	Min.	Typ.	Max.	Units								
Frequency Range		-	970	-	1050	MHz								
Step Size		-	-	100	-	kHz								
Settling Time		Within ± 1 kHz	-	2	-	mSec								
Output Power		-	-2.5	0	+3.5	dBm								
SSB Phase Noise		@ 100 Hz offset	-	-81	-	dBc/Hz								
		@ 1 kHz offset	-	-81	-75									
		@ 10 kHz offset	-	-94	-89									
		@ 100 kHz offset	-	-126	-118									
		@ 1 MHz offset	-	-146	-139									
Integrated SSB Phase Noise		@ 50 Hz to 5 MHz	-	-41	-	dBc								
Reference Spurious Suppression		Ref. Freq. 10 MHz	-	-103	-85	dBc								
Comparison Spurious Suppression		Step Size 100 kHz	-	-83	-67									
Non - Harmonic Spurious Suppression		-	-	-90	-									
Harmonic Suppression		-	-	-36	-29									
VCO Supply Voltage		+5.00	+4.75	+5.00	+5.25	V								
PLL Supply Voltage		+5.00	+4.75	+5.00	+5.25									
VCO Supply Current		-	-	24	30	mA								
PLL Supply Current		-	-	8	15									
Reference Input (External)		Frequency	10 (square wave)	-	10	-	MHz							
		Amplitude	1.0	0.8	1.0	1.2	V _{P-P}							
		Input impedance	-	-	100	-	KΩ							
		Phase Noise @ 1 kHz offset	-	-	-145	-	dBc/Hz							
RF Output port Impedance		-	-	50	-	Ω								
Input Logic Level		Input high voltage	-	4.20	-	-	V							
		Input low voltage	-	-	-	0.95	V							
Digital Lock Detect		Locked	-	4.35	-	5.25	V							
		Unlocked	-	-	-	0.40	V							
Frequency Synthesizer PLL		-	ADF4118											
PLL Programming		-	3-wire serial 5V CMOS											
Register Map NOTE 1	F_Register NOTE 2	<i>Reserved</i>	<i>Power-Down 2</i>	<i>Reserved</i>	<i>Timer Counter Control</i>	<i>Fastlock Mode</i>	<i>Reserved</i>	<i>Fastlock Enable</i>	<i>CP 3-State</i>	<i>PD Polarity</i>	<i>Muxout Control</i>	<i>Power-Down 1</i>	<i>Counter Reset</i>	<i>Control Bits</i>
		0	0	000	0000	0	0	0	0	1	001	0	0	10
	N_Register @ 1050 MHz	<i>CP Gain</i>	<i>13-Bit B Counter</i>								<i>5-Bit A Counter</i>			<i>Control Bits</i>
		1	0000101001000								00100			01
R_Register	<i>Lock Detect Precision</i>	<i>Test Mode Bits</i>			<i>14-BIT Reference Counter, R</i>							<i>Control Bits</i>		
	1	0000			00000001100100							00		

Note 1: Registers Load Sequence: Initialization Register, F Register, R Register, N Register.

Note 2: For the Initialization Register use Register F with Control Bits 11.

Absolute Maximum Ratings

Parameters	Ratings
VCO Supply Voltage	6.3V
PLL Supply Voltage	6.3V
VCO Supply Voltage to PLL Supply Voltage	N.A.
Reference Frequency Voltage	-0.3Vmin, VCC PLL +0.3Vmax
Data, Clock, LE Levels	-0.3Vmin, VCC PLL +0.3Vmax
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

Permanent damage may occur if any of these limits are exceeded

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



NON-CATALOG

Frequency Synthesizer

KSN-1050A-119+

Typical Performance Data

FREQUENCY (MHz)	POWER OUTPUT (dBm)			VCO CURRENT (mA)			PLL CURRENT (mA)		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
	970	0.03	0.00	-0.03	23.46	24.46	25.28	6.77	8.19
980	-0.01	-0.02	-0.03	23.49	24.49	25.32	6.80	8.19	9.52
990	-0.03	-0.04	-0.03	23.52	24.51	25.36	6.81	8.21	9.52
1000	-0.04	-0.03	-0.02	23.54	24.54	25.39	6.82	8.22	9.54
1010	-0.04	-0.02	-0.02	23.55	24.56	25.41	6.83	8.23	9.54
1020	-0.07	-0.04	-0.04	23.58	24.57	25.43	6.84	8.24	9.56
1030	-0.12	-0.08	-0.10	23.59	24.59	25.45	6.85	8.24	9.57
1040	-0.17	-0.15	-0.16	23.61	24.61	25.47	6.82	8.23	9.55
1050	-0.27	-0.23	-0.24	23.63	24.62	25.49	6.83	8.23	9.56

FREQUENCY (MHz)	HARMONICS (dBc)					
	F2			F3		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
970	-33.87	-36.66	-40.60	-47.91	-50.89	-53.08
980	-33.98	-36.28	-39.75	-48.48	-50.54	-51.65
990	-34.48	-36.61	-39.76	-48.65	-51.51	-52.79
1000	-35.19	-37.42	-40.06	-47.40	-50.69	-51.66
1010	-35.13	-37.09	-39.63	-47.17	-49.84	-51.45
1020	-35.44	-37.30	-39.70	-46.79	-48.37	-50.78
1030	-36.04	-37.61	-39.88	-45.54	-48.59	-49.98
1040	-36.35	-38.26	-39.96	-44.16	-47.24	-47.03
1050	-36.25	-37.85	-39.94	-43.18	-46.46	-47.22

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



NON-CATALOG

Frequency Synthesizer

KSN-1050A-119+

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	+25°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
970	-84.42	-82.31	-94.49	-125.67	-146.68
980	-86.62	-80.81	-94.94	-126.21	-147.08
990	-83.71	-82.36	-94.21	-126.40	-147.39
1000	-84.14	-83.64	-93.26	-125.98	-147.13
1010	-83.38	-81.96	-94.27	-125.50	-146.51
1020	-81.90	-80.90	-94.80	-126.41	-146.39
1030	-85.71	-81.04	-93.73	-126.28	-147.20
1040	-83.28	-82.61	-93.88	-126.20	-146.29
1050	-84.98	-80.77	-93.65	-126.26	-146.88

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	-45°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
970	-82.06	-80.36	-94.50	-125.19	-148.05
980	-83.34	-82.15	-94.13	-126.98	-148.61
990	-81.63	-81.63	-94.20	-127.34	-149.22
1000	-81.57	-80.44	-94.19	-127.40	-147.20
1010	-82.92	-83.31	-93.22	-127.28	-148.87
1020	-83.83	-80.75	-95.01	-127.55	-148.89
1030	-81.97	-80.90	-94.13	-127.35	-149.08
1040	-81.16	-81.28	-93.99	-127.27	-147.44
1050	-83.16	-81.47	-94.47	-127.25	-145.67

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	+85°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
970	-81.46	-80.87	-94.29	-123.26	-143.20
980	-80.93	-79.91	-94.60	-123.78	-142.50
990	-82.99	-82.44	-93.51	-124.09	-142.99
1000	-82.38	-80.67	-93.10	-124.17	-144.12
1010	-81.51	-81.68	-93.97	-124.43	-144.93
1020	-81.61	-80.38	-93.55	-124.57	-144.83
1030	-81.71	-81.89	-93.84	-124.51	-144.52
1040	-82.44	-82.09	-93.25	-124.41	-145.25
1050	-85.11	-80.97	-93.33	-124.38	-145.16

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



NON-CATALOG

Frequency Synthesizer

KSN-1050A-119+

COMPARISON SPURIOUS ORDER	COMPARISON SPURIOUS @ Fcarrier 970MHz+(n*Freference) (dBc) note 1			COMPARISON SPURIOUS @ Fcarrier 1010MHz+(n*Freference) (dBc) note 1			COMPARISON SPURIOUS @ Fcarrier 1050MHz+(n*Freference) (dBc) note 1		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
n									
-5	-106.67	-104.22	-97.73	-97.21	-104.79	-95.13	-96.59	-95.73	-101.22
-4	-107.41	-106.08	-94.36	-96.65	-103.50	-91.38	-95.03	-92.36	-104.31
-3	-103.51	-101.28	-94.63	-92.24	-102.07	-89.14	-89.90	-88.76	-98.20
-2	-95.00	-96.65	-90.56	-89.84	-95.43	-84.24	-86.64	-85.79	-92.48
-1	-88.35	-85.57	-81.33	-83.70	-84.96	-78.22	-79.80	-81.38	-82.43
0 ^{note 2}	-	-	-	-	-	-	-	-	-
+1	-86.53	-87.12	-82.76	-81.10	-84.96	-78.79	-82.84	-83.46	-82.83
+2	-95.28	-96.08	-88.72	-87.09	-94.43	-84.50	-90.28	-88.51	-93.90
+3	-101.88	-99.70	-93.69	-90.76	-104.26	-89.67	-91.18	-87.96	-101.65
+4	-107.58	-105.35	-96.50	-93.79	-103.21	-91.00	-94.27	-94.17	-103.41
+5	-111.85	-103.02	-97.82	-95.75	-100.10	-95.04	-97.20	-94.56	-103.03

Note 1: Comparison frequency 100 kHz

Note 2: All spurs are referenced to carrier signal (n=0).

REFERENCE SPURIOUS ORDER	REFERENCE SPURIOUS @ Fcarrier 970MHz+(n*Freference) (dBc) note 3			REFERENCE SPURIOUS @ Fcarrier 1010MHz+(n*Freference) (dBc) note 3			REFERENCE SPURIOUS @ Fcarrier 1050MHz+(n*Freference) (dBc) note 3		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
n									
-5	-125.32	-108.38	-112.03	-109.11	-110.81	-109.81	-121.51	-107.01	-111.73
-4	-102.94	-110.11	-114.42	-107.45	-118.18	-123.47	-103.87	-110.56	-115.80
-3	-116.07	-110.77	-112.90	-118.88	-112.05	-109.49	-114.85	-110.00	-110.93
-2	-103.97	-112.26	-113.25	-109.08	-113.92	-118.93	-101.78	-108.95	-113.42
-1	-108.65	-107.04	-104.69	-110.29	-103.69	-110.59	-110.13	-107.25	-110.91
0 ^{note 4}	-	-	-	-	-	-	-	-	-
+1	-106.35	-107.17	-103.05	-104.55	-103.13	-108.04	-105.81	-110.77	-112.40
+2	-109.33	-110.68	-109.10	-105.29	-111.86	-110.12	-109.11	-109.98	-108.38
+3	-112.93	-110.46	-116.62	-112.42	-108.99	-107.92	-114.60	-111.42	-112.65
+4	-104.86	-108.58	-113.55	-107.21	-119.35	-112.41	-104.99	-108.85	-111.67
+5	-115.59	-110.19	-109.07	-111.63	-114.70	-110.85	-111.17	-108.70	-113.34

Note 3: Reference frequency 10 MHz




Note 4: All spurs are referenced to carrier signal (n=0).

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp








Typical Performance Curves



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp











Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Pin Configuration




Pin Connection

Pin Number	Function
1	VCC PLL
2	GND
3	REF IN
4	GND
5	VCC VCO
6	GND
7	RF OUT
8	GND
9	LOCK DET
10	CLOCK
11	DATA
12	LE
13	GND
14	GND

Recommended Application Circuit


Note: REF IN and RF OUT ports are internally AC coupled.



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Device Marking



Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

Case Style: DK1042

Tape & Reel: TR-F28

Suggested Layout for PCB Design: PL-249

Evaluation Board: TB-567+

Environment Ratings: ENV03T2

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp