

Non-Catalog Model

Frequency Mixer

LRMS-2UHJ

Level 17 (LO Power +17 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : QQQ569

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	10		1000	MHz
	RF (fL to fU)	10		1000	MHz
	IF	10		750	MHz
Conversion Loss	mid band		7.1	9.2	dB
	Total Range			9.9	dB
LO-RF Isolation	Low Range	40	50		dB
	Mid Range	30	38		dB
	Upper Range	23	30		dB
LO-IF Isolation	Low Range	30	50		dB
	Mid Range	25	40		dB
	Upper Range	22	34		dB
1 dB Comp. Input Power			+14		dBm

Notes: Low Range = [fL to 10fL]
mid band = [2fL to fU/2]


Mid Range = [10fL to fU/2]

Upper Range = [fU/2 to fU]

Phase detection, positive polarity
Aqueous washable.

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA

Electrical Schematics



PIN CONNECTIONS	
LO	1
RF	4
IF	5
GROUND	2, 3, 6