

Frequency Mixer

MWJ-ED14276/1

Level 17 (LO Power + 17 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



CASE STYLE : 99-01-1410

Please click "Back", and then click "Contact Us" for Applications support.

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	324		474	MHz
	RF (fL to fU)	100		250	MHz
	IF	30		300	MHz
Conversion Loss	Total Range		8		dB
LO-RF Isolation			48		dB
LO-IF Isolation			47		dB
Input IP3			+31		dBm
1 dB Compression			+20		dBm

MAXIMUM RATINGS	
Operating Temperature	-45°C to +85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	13
RF	21
IF	2
OPEN	10
GROUND	1,3,4,5,6,7,8,9,11,12,14,15,16,17,18,19,20,22

