NON-CATALOG

Low Pass Filter

LFCN-95

 50Ω

DC⁽¹⁾ to 95 MHz

Generic photo used for illustration purposes only

CASE STYLE: FV1206


Maximum Ratings


| Operating Temperature | -55°C to 100°C |
|-----------------------|------------------|
| Storage Temperature | -55°C to 100°C |
| RF Power Input* | 8 5W max at 25°C |

^{*} Passband rating, derate linearly to 3.5W at 100°C ambient Permanent damage may occur if any of these limits are exceeded.

Pin Connections

| RF IN | 1_ |
|--------|-----|
| RF OUT | 3 |
| GROUND | 2.4 |






Suggested Layout, Tolerance to be within ±.002

Outline Dimensions (inch)

| A .126 3.20 | B .063 1.60 | C .037 0.94 | .020 0.51 | E .032 0.81 | F .009 0.23 | G .169 4.29 | |
|-------------------|-------------------|-------------------|--------------|-------------------|-------------------|-------------------|-------------|
| H .087 | J .024 | .122 | .024 | M .087 | N .012 | | wt grams |
| 2.21 | 0.61 | 3.10 | 0.61 | 2.21 | 0.30 | 1.80 | .020 |

Demo Board MCL P/N: TB-270 Suggested PCB Layout (PL-137)



COPLANAR WAYEGUIDE PARAMETERS ARE SHOWN FOR ROGERS ROA\$50B WITH THICKNESS .020" ± .0015". COPPER: 1/2 02. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED. NOTES: 1.

DENOTES DESCRIPTION OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- excellent power handling, 8.5W
- small size
- 7 sections
- temperature stable
- LTCC construction
- protected by U.S. Patent 6,943,646

Applications


- harmonic rejection
- VHF/UHF transmitters/receivers

Electrical Specifications(1,2) at 25°C


| Pa | rameter | F# | Frequency (MHz) | Min. | Тур. | Max. | Unit |
|-----------|----------------|-------|-----------------|------|------|------|------|
| | Insertion Loss | DC-F1 | DC-95 | _ | _ | 1.0 | dB |
| Pass Band | Freq. Cut-Off | F2 | 165 | _ | 3.0 | _ | dB |
| | VSWR | DC-F1 | DC-95 | _ | 1.2 | _ | :1 |
| Sten Bend | Rejection Loss | F3 | 240 | 20 | _ | _ | dB |
| | | F4-F5 | 255-1600 | _ | 40 | _ | dB |
| Stop Band | | F6 | 4500 | _ | 20 | _ | dB |
| | VSWR | F3-F6 | 240-4500 | _ | 20 | _ | :1 |

- (1) In Application where DC voltage is present at either input or output ports, coupling capacitors are required.
- (2) Measured on Mini-Circuits Characterization Test Board TB-270.

Typical Frequency Response





Electrical Schematic



Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|--------------------|------------------------|--------------|
| 10.00 | 0.30 | 1.06 |
| 95.00 | 0.83 | 1.07 |
| 165.00 | 2.56 | 1.79 |
| 180.00 | 4.08 | 2.58 |
| | 17.29 | 8.75 |
| 220.00 | | |
| 240.00 | 30.37 | 11.55 |
| 250.00 | 36.66 | 12.43 |
| 410.00 | 55.58 | 23.11 |
| 700.00 | 53.60 | 50.04 |
| 1235.00 | 44.98 | 76.58 |
| 1600.00 | 39.94 | 68.40 |
| 2000.00 | 33.54 | 63.70 |
| 2500.00 | 27.39 | 48.12 |
| 4500.00 | 20.96 | 24.63 |
| 5000.00 | 19.57 | 21.89 |
| 5550.00 | 10.57 | 21.00 |





- Notes
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp