


Frequency Mixer WIDE BAND

MCA1T-42LH+

Level 10 (LO Power+10 dBm) 1000 to 4200 MHz



CASE STYLE: DZ885-2

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-40°C to 85°C
RF Power	50 mW
IF Current	40 mA

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

LO	10
RF	5
IF	3
GROUND	1,2,4,6,7,8,9


Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	E	F	G
.350	.280	.095	.075	.050	.030
8.89	7.11	2.41	1.91	1.27	0.76
H	K	L	M	wt	
.074	.096	.321	.030	grams	
1.88	2.44	8.15	0.76	0.21	

Demo Board MCL P/N: TB-493+ Suggested PCB Layout (PL-288)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
■ DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
▨ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wide bandwidth, 1000 to 4200 MHz
- low conversion loss, 6.0 dB typ.
- excellent L-R isolation, 38 dB typ.
- LTCC double balanced mixer
- aqueous washable
- low cost
- low profile, 0.095"
- protected by US Patent 7,027,795^A, 8,749,989

Applications

- cellular
- PCN
- fixed satellite
- WCDMA
- defense radar
- defense communications

Electrical Specifications (T_{AMB}=-40°C to 85°C)


FREQUENCY (MHz)	CONVERSION LOSS (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		IP3 at center band (dBm)			
	LO/RF f _c -f _u	IF	σ	Max.	Typ.	Min.	Typ.		Min.		
1000-4200	DC-1500			6.0	0.1	8.9	38	23	20	11	12

1 dB COMPR. +5 dBm typ.

Typical Performance Data

Frequency (MHz)	Conversion Loss (dB)		Isolation L-R (dB)		Isolation L-I (dB)		VSWR RF Port (:1)		VSWR LO Port (:1)	
	LO	+10dBm	LO	+10dBm	LO	+10dBm	LO	+10dBm	LO	+10dBm
1000.10	1030.10	6.55	34.13	21.54	2.14	5.34				
1200.10	1230.10	5.97	43.05	23.49	2.95	2.96				
1500.10	1530.10	5.49	37.05	21.39	2.84	2.57				
2000.10	2030.10	6.09	39.22	22.41	2.57	2.93				
2200.10	2230.10	6.10	38.41	20.53	2.50	3.47				
2500.00	2530.00	5.83	44.08	19.19	2.17	3.86				
3000.10	3030.10	5.23	49.42	23.08	1.78	3.37				
3500.10	3530.10	5.48	32.83	25.91	1.56	1.72				
4000.10	4030.10	6.81	31.85	26.26	3.18	3.03				
4200.10	4230.10	7.86	34.53	19.79	3.76	3.54				









Electrical Schematic



NON-CATALOG

Performance Charts

MCA1T-42LH+



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

