<u>2 Way-90° Power Splitter</u>

540 to 980 MHz 500





CASE STYLE: GE0805C-1

The Big Deal

- •High Power handling (15W)
- •Low Unbalance, 0.3 dB & 2 deg. typ.
- Industry leading combination of size/bandwidth

Product Overview

Mini-Circuits new 90° Power Splitter, model: QCS-981+, offers an industry leading combination of operating bandwidth and size; supporting nearly an octave band in a miniature EIA-0805 form factor. The outstanding phase and amplitude unbalance make this component a versatile building block for use in a variety of systems and sub-system designs.

Kev Features

| Feature | Advantages | | |
|-----------------------------------|---|--|--|
| Small Size | Offered in the EIA-0805 package size, the QCS-981+ offers an industry leading combination of size, bandwidth and frequency. The small footprint (2.0mm x1.25mm) allows for reduced parasitics in systems with improved performance and simplified layout. | | |
| Low Phase and Amplitude Unbalance | Supporting 2 deg. and 0.3 dB unbalance make this 90° hybrid applicable for use in high- er level integrated components such as image reject mixers, single sideband modulators, phase shifters, variable attenuators, and balance amplifiers. | | |
| High Power Handling | Capable of operating up to 15W, the LTCC construction of the QCS-981+ makes this 90° hybrid a robust, rugged product that can be used effectively in either the transmit or receive paths. | | |

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Ultra-Small Ceramic LTCC **Power Splitter/Combiner**

2 Way-90° 540 to 980 MHz 50Ω


Maximum Ratings

| Operating Temperature | -55°C to 100°C |
|--|----------------|
| Storage Temperature | -55°C to 100°C |
| Power Input (as a splitter) | 15W* max. |
| *Derate linearly to 7W at 100°C ambient. | |

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

| SUM PORT | 1 |
|----------------------|-----|
| PORT 1 (0°) | 4 |
| PORT 2 (+90°) | 6 |
| GROUND | 2,5 |
| 50 OHM TERM EXTERNAL | 3 |



Outline Dimensions (inch)

| | | | | • • | |
|------|------|------|------|------|-------|
| Α | В | С | D | E | F |
| .079 | .049 | .033 | .014 | .012 | .012 |
| 2.01 | 1.24 | 0.84 | 0.36 | 0.30 | 0.30 |
| G | н | J | к | | wt |
| - | | - | | | vvl |
| .026 | .014 | .039 | .110 | | grams |
| 0.66 | 0.36 | 1.00 | 2.80 | | .008 |

Electrical Schematic

50 Ohm

SUM PORT

PORT 2

PORT 1

Notes

Features

- Low insertion loss, 0.6 dB typ.
- High isolation, 18 dB typ.
- Miniature size, 0.079"x0.049"x0.033"

Phase Shifter

Point to Point

Attenuator

- LTCC construction
- High power

Applications

- Balanced amplifiers
- Modulators
- DCS, PCS, UMTS
- WiMax
- WiFi ISM

QCS-981+




Generic photo used for illustration purposes only CASE STYLE: GE0805C-1

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Electrical Specifications at 25°C

| Parameter | Frequency (MHz) | Min. | Тур. | Max. | Unit | |
|--------------------------------------|-----------------|------|---------|------|--------|--|
| Frequency | | 540 | | 980 | MHz | |
| | 540-700 | — | 0.4 | 0.8 | | |
| Insertion Loss | 700-800 | _ | 0.5 0.8 | | dB | |
| (Avg. Of Coupled Outputs) above 3 dB | 800-900 | _ | 0.7 | 0.9 | uв | |
| | 900-980 | _ | 0.9 | 1.4 | | |
| | 540-700 | 17 | 21 | _ | | |
| Isolation | 700-800 | 17 | 20 | _ | dB | |
| | 800-900 | 16 | 19 | _ | uв | |
| | 900-980 | 14 | 17 | | | |
| | 540-700 | _ | 2 | 4 | Degree | |
| Phase Unbalance | 700-800 | _ | 2 | 4 | | |
| | 800-900 | _ | 1 | 4 | | |
| | 900-980 | | 3 | 6 | | |
| | 540-700 | _ | 0.8 | 1.4 | | |
| Amplitude Unbalance | 700-800 | _ | 0.35 | 0.8 | dB | |
| Amplitude onbalance | 800-900 | _ | 0.3 | 0.7 | | |
| | 900-980 | | 1.2 | 1.6 | | |
| VSWR (Port S) | 540-980 | _ | 1.4 | 1.6 | :1 | |
| VSWR (Port 1-2) | 540-980 | _ | 1.5 | 1.7 | :1 | |



A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp





QCS-981+


| | <i>,</i> , | | | | | | | |
|--------------------|---------------------------------|------|--------------------------------|-------------------|------------------------------|-----------|-----------|-----------|
| Frequency (MHz) | Total Loss ¹ (dB) | | Amplitude Unbalance (dB) | Isolation (dB) | Phase Unbalance (deg.) | VSWR S | VSWR 1 | VSWR 2 |
| | S-1 | S-2 | | | | | | |
| 540.00 | 3.82 | 3.00 | 0.82 | 21.38 | 88.48 | 1.18 | 1.11 | 1.21 |
| 600.00 | 3.56 | 3.26 | 0.30 | 21.34 | 88.62 | 1.18 | 1.11 | 1.21 |
| 620.00 | 3.50 | 3.33 | 0.17 | 21.31 | 88.67 | 1.18 | 1.11 | 1.21 |
| 660.00 | 3.39 | 3.45 | 0.06 | 21.19 | 88.80 | 1.18 | 1.12 | 1.21 |
| 700.00 | 3.33 | 3.56 | 0.22 | 21.04 | 88.97 | 1.18 | 1.14 | 1.22 |
| 720.00 | 3.32 | 3.60 | 0.27 | 20.92 | 89.05 | 1.18 | 1.15 | 1.23 |
| 760.00 | 3.31 | 3.65 | 0.34 | 20.61 | 89.24 | 1.19 | 1.18 | 1.24 |
| 800.00 | 3.36 | 3.68 | 0.32 | 20.23 | 89.54 | 1.20 | 1.22 | 1.26 |
| 820.00 | 3.39 | 3.68 | 0.28 | 20.00 | 89.70 | 1.21 | 1.24 | 1.27 |
| 860.00 | 3.51 | 3.66 | 0.15 | 19.42 | 90.10 | 1.23 | 1.28 | 1.30 |
| 880.00 | 3.59 | 3.63 | 0.05 | 19.09 | 90.37 | 1.24 | 1.31 | 1.32 |
| 900.00 | 3.68 | 3.60 | 0.08 | 18.72 | 90.68 | 1.25 | 1.34 | 1.34 |
| 920.00 | 3.80 | 3.57 | 0.24 | 18.34 | 91.05 | 1.27 | 1.37 | 1.37 |
| 960.00 | 4.10 | 3.47 | 0.63 | 17.46 | 91.98 | 1.32 | 1.44 | 1.44 |
| 980.00 | 4.29 | 3.42 | 0.88 | 16.98 | 92.62 | 1.35 | 1.49 | 1.47 |

Typical Performance Data

1. Total Loss = Insertion Loss + 3dB splitter loss.







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

###