

NON-CATALOG

Surface Mount

Voltage Controlled Oscillator

MOS-958-119+

5V Tuning for PLL IC's 958 MHz



CASE STYLE: CZ682

Features

- linear tuning characteristics
- low phase noise
- low pulling
- low pushing
- aqueous washable

Applications

- wireless communications
- converter

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

| MODEL NO. | FREQ. (MHz) | | POWER OUTPUT (dBm) | PHASE NOISE dBc/Hz SSB at offset frequencies, kHz | | | | TUNING | | | | | NON HARMONIC SPURIOUS (dBc) | HARMONICS (dBc) | | PULLING pk-pk @12 dB (MHz) | PUSHING (MHz/V) | DC OPERATING POWER | |
|--------------|-------------|------|--------------------|---|------|------|------|--------|-------------------|---------------------|---------------|---------------------------------|-----------------------------|-----------------|------|----------------------------|-----------------|--------------------|------|
| | Min. | Max. | | Typ. | 1 | 10 | 100 | 1000 | VOLTAGE RANGE (V) | SENSITIVITY (MHz/V) | PORT CAP (pF) | 3 dB MODULATION BANDWIDTH (MHz) | | Typ. | Max. | | | Typ. | Max. |
| MOS-958-119+ | | 958 | +2 | -88 | -113 | -133 | -153 | 0.3 | 3.5 | 13 | 34 | 60 | -90 | -22 | -12 | 0.8 | 0.1 | 5 | 40 |

Pin Connections


| | |
|--------|-----------|
| RF OUT | 5 |
| VCC | 3 |
| V-TUNE | 1 |
| GROUND | 2,4,6,7,8 |

Maximum Ratings


| | |
|--------------------------------------|----------------|
| Operating Temperature | -55°C to 85°C |
| Storage Temperature | -55°C to 100°C |
| Absolute Max. Supply Voltage (Vcc) | 6.0V |
| Absolute Max. Tuning Voltage (Vtune) | 5.5V |
| All specifications | 50 ohm system |

Permanent damage may occur if any of these limits are exceeded.

Outline Drawing



Demo Board MCL P/N: TB-128 Suggested PCB Layout (PL-023)



- NOTE: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Outline Dimensions (inch mm)

| A | B | C | D | E | F | G | H | J | K | L | M | N | P | Q | wt. |
|------|------|------|------|------|------|------|------|-------|------|------|-------|------|------|------|-------|
| .375 | .375 | .131 | .188 | .035 | .033 | .154 | .050 | .425 | .183 | .060 | .425 | .028 | .154 | .060 | grams |
| 9.52 | 9.52 | 3.33 | 4.77 | 0.89 | 0.84 | 3.91 | 1.27 | 10.80 | 4.65 | 1.52 | 10.80 | 0.71 | 3.91 | 1.52 | .60 |



For detailed performance specs & shopping online see web site

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.

REV. D
M149087
EDR-8950F1
MOS-958-119+
RAV
141223
Page 1 of 2







NON-CATALOG

Performance Data & Curves*

MOS-958-119+

| V TUNE | TUNE SENS (MHz/V) | FREQUENCY (MHz) | | | POWER OUTPUT (dBm) | | | Icc (mA) | HARMONICS (dBc) | | | FREQ. PUSH (MHz/V) | FREQ. PULL (MHz) | PHASE NOISE (dBc/Hz) at offsets | | | | FREQ OFFSET (KHz) | PHASE NOISE at 958 MHz (dBc/Hz) |
|--------|-------------------|-----------------|-------|-------|--------------------|-------|-------|----------|-----------------|-------|-------|--------------------|------------------|---------------------------------|--------|--------|--------|-------------------|---------------------------------|
| | | -55°C | +25°C | +85°C | -55°C | +25°C | +85°C | | F2 | F3 | F4 | | | 1kHz | 10kHz | 100kHz | 1MHz | | |
| 0.00 | 16.00 | 929.5 | 925.8 | 922.3 | 2.75 | 2.31 | 1.30 | 33.02 | -31.8 | -26.4 | -42.5 | 0.33 | 0.62 | -89.9 | -112.6 | -134.2 | -153.4 | 1.0 | -87.17 |
| 0.30 | 14.15 | 934.1 | 930.5 | 927.1 | 2.73 | 2.29 | 1.30 | 33.02 | -31.2 | -26.0 | -41.5 | 0.19 | 0.62 | -87.9 | -112.8 | -134.4 | -151.4 | 2.0 | -96.58 |
| 0.50 | 13.46 | 936.9 | 933.4 | 930.0 | 2.71 | 2.27 | 1.30 | 33.01 | -30.9 | -25.6 | -41.1 | 0.14 | 0.63 | -86.4 | -113.7 | -134.2 | -153.6 | 3.5 | -102.96 |
| 0.75 | 13.00 | 940.3 | 936.7 | 933.4 | 2.68 | 2.24 | 1.27 | 33.00 | -30.4 | -25.3 | -39.9 | 0.10 | 0.65 | -87.5 | -113.6 | -134.3 | -154.0 | 6.0 | -108.11 |
| 1.00 | 12.76 | 943.5 | 940.0 | 936.6 | 2.65 | 2.21 | 1.26 | 33.00 | -30.0 | -25.2 | -39.3 | 0.08 | 0.66 | -87.9 | -114.0 | -134.7 | -153.9 | 8.5 | -111.38 |
| 1.25 | 12.67 | 946.7 | 943.2 | 939.8 | 2.62 | 2.17 | 1.24 | 32.98 | -29.6 | -25.0 | -39.4 | 0.07 | 0.67 | -88.5 | -112.7 | -134.3 | -154.1 | 10.0 | -113.07 |
| 1.50 | 12.66 | 949.9 | 946.3 | 942.9 | 2.58 | 2.14 | 1.23 | 32.97 | -29.3 | -25.0 | -39.3 | 0.05 | 0.68 | -89.3 | -113.3 | -134.5 | -153.5 | 20.8 | -120.08 |
| 1.75 | 12.73 | 953.1 | 949.5 | 946.1 | 2.55 | 2.11 | 1.20 | 32.97 | -29.0 | -25.0 | -39.2 | 0.05 | 0.70 | -87.6 | -113.9 | -134.6 | -153.8 | 35.5 | -125.05 |
| 2.00 | 12.82 | 956.2 | 952.7 | 949.2 | 2.52 | 2.07 | 1.18 | 32.96 | -28.7 | -25.1 | -39.2 | 0.05 | 0.72 | -88.5 | -113.1 | -134.3 | -153.9 | 60.7 | -130.14 |
| 2.25 | 12.92 | 959.4 | 955.9 | 952.4 | 2.48 | 2.03 | 1.15 | 32.95 | -28.4 | -25.0 | -39.0 | 0.06 | 0.74 | -87.5 | -113.4 | -134.6 | -153.5 | 85.2 | -132.83 |
| 2.50 | 13.02 | 962.7 | 959.1 | 955.6 | 2.45 | 1.99 | 1.12 | 32.94 | -28.0 | -24.9 | -39.1 | 0.07 | 0.75 | -89.8 | -113.5 | -134.5 | -154.5 | 100.0 | -134.04 |
| 2.75 | 13.11 | 965.9 | 962.4 | 958.9 | 2.43 | 1.95 | 1.10 | 32.93 | -27.6 | -24.8 | -38.8 | 0.09 | 0.76 | -87.9 | -113.3 | -134.3 | -153.0 | 200.6 | -140.46 |
| 3.00 | 13.16 | 969.2 | 965.6 | 962.1 | 2.40 | 1.92 | 1.07 | 32.92 | -27.2 | -24.7 | -38.5 | 0.12 | 0.76 | -87.9 | -113.6 | -134.2 | -152.6 | 330.7 | -144.50 |
| 3.25 | 13.19 | 972.4 | 968.9 | 965.4 | 2.39 | 1.89 | 1.05 | 32.91 | -27.0 | -24.5 | -37.9 | 0.15 | 0.75 | -87.5 | -112.8 | -134.3 | -153.9 | 554.9 | -149.11 |
| 3.50 | 13.19 | 975.7 | 972.2 | 968.7 | 2.37 | 1.86 | 1.02 | 32.90 | -26.8 | -24.4 | -37.9 | 0.18 | 0.73 | -87.6 | -112.9 | -134.2 | -153.8 | 1000.0 | -154.37 |

*at 25°C unless mentioned otherwise



For detailed performance specs & shopping online see web site

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.