

Non-Catalog Model

Frequency Mixer

ROK-2500LH

Level 10 (LO Power +10 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : PP230

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	1		2500	MHz
	RF (fL to fU)	1		2500	MHz
	IF	0		500	MHz
Conversion Loss	mid band		6.4	8.4	dB
	Total Range			9.0	dB
LO-RF Isolation	Low Range	40	55		dB
	Mid Range	20	48		dB
	Upper Range	20	30		dB
LO-IF Isolation	Low Range	38	55		dB
	Mid Range	15	27		dB
	Upper Range	15	22		dB
1 dB Comp. Input Power			+5		dBm

Notes: Low Range = [fL to 10fL]
mid band = [2fL to fU/2]

Mid Range = [10fL to fU/2]

Upper Range = [fU/2 to fU]

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	4
RF	2
IF	1
GROUND	3

Electrical Schematics

