

## Voltage Controlled Oscillator

ROS-1150C-119+

Ultra Low Noise 1146 to 1154 MHz

## Features

- ultra low phase noise
- linear tuning characteristics
- very low pushing
- very low pulling
- aqueous washable

## Applications

- wireless communications
- airborne telecom system



CASE STYLE: CK1113

## +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Electrical Specifications

| MODEL NO.      | FREQ. (MHz) |      | POWER OUTPUT (dBm) | PHASE NOISE dBc/Hz SSB at offset frequencies,kHz |      |      |      | TUNING |      |      |      |      | NON HARMONIC SPURIOUS (dBc) | HARMONICS (dBc) |      | PULLING pk-pk @12 dB <sub>r</sub> (MHz) | PUSHING (MHz/V) | DC OPERATING POWER |      |      |                         |              |
|----------------|-------------|------|--------------------|--------------------------------------------------|------|------|------|--------|------|------|------|------|-----------------------------|-----------------|------|-----------------------------------------|-----------------|--------------------|------|------|-------------------------|--------------|
|                | Min.        | Max. |                    | 1                                                | 10   | 100  | 1000 | Min.   | Max. | Typ. | Typ. | Typ. |                             | Typ.            | Typ. |                                         |                 | Max.               | Typ. | Typ. | V <sub>cc</sub> (volts) | Current (mA) |
|                |             |      |                    |                                                  |      |      |      |        |      |      |      |      |                             |                 |      |                                         |                 |                    |      |      |                         |              |
|                |             |      |                    |                                                  |      |      |      |        |      |      |      |      |                             |                 |      |                                         |                 |                    |      |      |                         |              |
| ROS-1150C-119+ | 1146        | 1154 | +2.5               | -98                                              | -121 | -141 | -160 | 0.5    | 11   | 3    | 55   | 45   | -90                         | -20             | -10  | 0.1                                     | 0.1             | 5                  | 35   |      |                         |              |

## Pin Connections



|        |                                |
|--------|--------------------------------|
| RF OUT | 10                             |
| VCC    | 14                             |
| V-TUNE | 2                              |
| GROUND | 1,3,4,5,6,7,8,9,11,12,13,15,16 |

## Maximum Ratings

|                                      |                |
|--------------------------------------|----------------|
| Operating Temperature                | -55°C to 85°C  |
| Storage Temperature                  | -55°C to 100°C |
| Absolute Max. Supply Voltage (Vcc)   | 6.5V           |
| Absolute Max. Tuning Voltage (Vtune) | 13.0V          |
| All specifications                   | 50 ohm system  |

Permanent damage may occur if any of these limits are exceeded.

## Outline Drawing


**Demo Board MCL P/N: TB-10**  
**Suggested PCB Layout (PL-012)**


## NOTES:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .030"  $\pm$  .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE BOTTOM IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## Outline Dimensions (inch mm)

| A     | B     | C    | D    | E    | F    | G    | H    | J     | K    | L    | M    | N    | P    | Q    | R    | S    | T    | wt.   |
|-------|-------|------|------|------|------|------|------|-------|------|------|------|------|------|------|------|------|------|-------|
| .500  | .500  | .220 | .100 | .080 | .115 | .060 | .040 | .540  | .060 | .100 | .135 | .135 | .115 | .140 | .070 | .150 | .070 | grams |
| 12.70 | 12.70 | 5.59 | 2.54 | 2.03 | 2.92 | 1.52 | 1.02 | 13.72 | 1.52 | 2.54 | 3.43 | 3.43 | 2.92 | 3.56 | 1.78 | 3.81 | 1.78 | 1.2   |

# NON-CATALOG

## Performance Data & Curves\*

## ROS-1150C-119+

| V<br>TUNE | TUNE<br>SENS<br>(MHz/V) | FREQUENCY<br>(MHz) |        |        | POWER OUTPUT<br>(dBm) |       |       | Icc<br>(mA) | HARMONICS (dBc) |       |       | FREQ.<br>PUSH<br>(MHz/V) | FREQ.<br>PULL<br>(MHz) | PHASE NOISE (dBc/Hz)<br>at offsets |        |        |        | FREQ<br>OFFSET<br>(KHz) | PHASE<br>NOISE at<br>1150 MHz<br>(dBc/Hz) |
|-----------|-------------------------|--------------------|--------|--------|-----------------------|-------|-------|-------------|-----------------|-------|-------|--------------------------|------------------------|------------------------------------|--------|--------|--------|-------------------------|-------------------------------------------|
|           |                         | -55°C              | +25°C  | +85°C  | -55°C                 | +25°C | +85°C |             | F2              | F3    | F4    |                          |                        | 1KHz                               | 10KHz  | 100KHz | 1MHz   |                         |                                           |
| 0.00      | 5.12                    | 1139.7             | 1137.4 | 1135.5 | 1.66                  | 2.27  | 2.47  | 23.14       | -24.4           | -26.0 | -41.3 | 0.01                     | 0.06                   | -96.8                              | -121.1 | -141.4 | -160.0 | 1.0                     | -98.27                                    |
| 0.50      | 4.13                    | 1142.1             | 1140.0 | 1138.2 | 1.73                  | 2.34  | 2.55  | 23.30       | -24.0           | -25.8 | -40.8 | 0.10                     | 0.07                   | -96.4                              | -120.6 | -141.6 | -160.1 | 2.0                     | -106.29                                   |
| 1.00      | 3.65                    | 1144.1             | 1142.1 | 1140.4 | 1.78                  | 2.39  | 2.60  | 23.42       | -23.5           | -25.7 | -40.4 | 0.12                     | 0.08                   | -98.9                              | -120.7 | -142.0 | -159.5 | 3.5                     | -111.77                                   |
| 1.50      | 3.37                    | 1145.8             | 1143.9 | 1142.2 | 1.83                  | 2.43  | 2.65  | 23.53       | -23.2           | -25.5 | -39.9 | 0.12                     | 0.08                   | -99.1                              | -121.0 | -141.0 | -160.3 | 6.0                     | -116.69                                   |
| 2.00      | 3.18                    | 1147.5             | 1145.6 | 1143.9 | 1.87                  | 2.47  | 2.69  | 23.64       | -22.9           | -25.4 | -40.1 | 0.12                     | 0.09                   | -98.2                              | -120.5 | -141.3 | -160.6 | 8.5                     | -120.09                                   |
| 2.50      | 3.07                    | 1149.1             | 1147.2 | 1145.6 | 1.91                  | 2.51  | 2.73  | 23.73       | -22.9           | -25.2 | -40.1 | 0.12                     | 0.09                   | -99.2                              | -121.3 | -142.9 | -158.8 | 10.0                    | -120.92                                   |
| 3.00      | 3.01                    | 1150.6             | 1148.7 | 1147.1 | 1.94                  | 2.54  | 2.76  | 23.83       | -22.4           | -25.0 | -40.1 | 0.12                     | 0.10                   | -99.4                              | -120.3 | -141.7 | -160.7 | 20.8                    | -127.75                                   |
| 3.50      | 2.98                    | 1152.1             | 1150.2 | 1148.6 | 1.97                  | 2.57  | 2.79  | 23.91       | -22.4           | -24.8 | -40.2 | 0.12                     | 0.10                   | -98.1                              | -121.6 | -141.5 | -160.1 | 35.5                    | -131.44                                   |
| 4.00      | 2.98                    | 1153.5             | 1151.7 | 1150.1 | 2.00                  | 2.60  | 2.82  | 24.00       | -21.8           | -24.6 | -40.2 | 0.12                     | 0.11                   | -99.2                              | -122.5 | -142.0 | -161.8 | 60.7                    | -136.84                                   |
| 4.50      | 2.99                    | 1155.0             | 1153.2 | 1151.6 | 2.03                  | 2.62  | 2.84  | 24.08       | -21.8           | -24.5 | -40.5 | 0.10                     | 0.11                   | -98.4                              | -120.8 | -140.8 | -160.0 | 86.7                    | -139.66                                   |
| 5.00      | 3.02                    | 1156.5             | 1154.7 | 1153.1 | 2.06                  | 2.64  | 2.85  | 24.16       | -21.2           | -24.3 | -40.4 | 0.10                     | 0.12                   | -98.0                              | -120.0 | -140.8 | -159.9 | 100.0                   | -141.17                                   |
| 5.50      | 3.06                    | 1158.0             | 1156.2 | 1154.6 | 2.08                  | 2.66  | 2.86  | 24.25       | -21.0           | -24.1 | -41.0 | 0.08                     | 0.12                   | -97.7                              | -119.8 | -141.6 | -160.2 | 148.1                   | -143.88                                   |
| 6.00      | 3.10                    | 1159.5             | 1157.7 | 1156.2 | 2.11                  | 2.68  | 2.87  | 24.32       | -21.0           | -24.0 | -41.1 | 0.06                     | 0.12                   | -96.1                              | -120.3 | -139.9 | -160.0 | 177.0                   | -144.59                                   |
| 6.50      | 3.14                    | 1161.1             | 1159.3 | 1157.7 | 2.13                  | 2.69  | 2.87  | 24.39       | -20.4           | -23.9 | -41.5 | 0.04                     | 0.13                   | -97.1                              | -120.2 | -141.1 | -158.9 | 211.6                   | -145.85                                   |
| 7.00      | 3.16                    | 1162.6             | 1160.8 | 1159.3 | 2.15                  | 2.69  | 2.87  | 24.45       | -20.1           | -23.8 | -41.6 | 0.02                     | 0.14                   | -97.4                              | -120.6 | -140.6 | -158.5 | 302.4                   | -147.89                                   |
| 7.50      | 3.15                    | 1164.2             | 1162.4 | 1160.9 | 2.17                  | 2.70  | 2.85  | 24.50       | -19.9           | -23.7 | -42.5 | 0.02                     | 0.15                   | -95.2                              | -118.9 | -140.8 | -159.6 | 361.5                   | -149.43                                   |
| 8.00      | 3.12                    | 1165.8             | 1164.0 | 1162.5 | 2.18                  | 2.69  | 2.83  | 24.54       | -19.6           | -23.7 | -43.5 | 0.08                     | 0.17                   | -95.6                              | -118.3 | -140.6 | -160.6 | 507.5                   | -153.77                                   |
| 9.00      | 2.95                    | 1168.9             | 1167.1 | 1165.6 | 2.19                  | 2.64  | 2.74  | 24.60       | -19.2           | -23.6 | -44.2 | 0.24                     | 0.19                   | -92.2                              | -117.6 | -139.8 | -159.1 | 606.7                   | -155.94                                   |
| 10.00     | 2.69                    | 1171.7             | 1170.0 | 1168.5 | 2.18                  | 2.56  | 2.62  | 24.60       | -19.0           | -23.6 | -42.7 | 0.38                     | 0.21                   | -92.8                              | -117.4 | -139.0 | -159.8 | 851.6                   | -158.34                                   |
| 11.00     | 2.41                    | 1174.3             | 1172.6 | 1171.2 | 2.11                  | 2.43  | 2.44  | 24.55       | -18.9           | -23.7 | -40.3 | 0.46                     | 0.22                   | -91.9                              | -115.6 | -139.1 | -158.7 | 1000.0                  | -160.15                                   |

\*at 25°C unless mentioned otherwise

