Surface Mount Switch

DC⁴ to 2.0 GHz 50 Ω SPDT, Reflective


Maximum Ratings

Operating Temperature	-40°C to 85°C						
Storage Temperature	-55°C to 100°C						
Input Power	see Note 1						
Control Current see Not Permanent damage may occur if any of these limits are exce							

Pin Connections

RF IN	1
RF OUT 1	6
RF OUT 2	3
CONTROL 1	5
CONTROL 2	4
GROUND	2,7,8


Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G
.163	.210	.077	.250	.220	.050	.017
4.14	5.33	1.96	6.35	5.59	1.27	0.43
H	J	K	M	N	P	wt
.009	.025	.030	.050	.030	.270	grams
0.23	0.64	0.76	1.27	0.76	6.86	0.10

Demo Board MCL P/N: TB-203 Suggested PCB Layout (PL-108) .080 .015 3X .050



NOTES: 1.TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2.BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- wideband, DC to 2.0 GHz
- very fast switching, 4ns typ.
- · low insertion loss, 0.5 dB typ.
- low video leakage, 15 mVp-p typ.

Applications

- cellular
- PCN
- · 2-way radio
- · receiver antenna switching





Generic photo used for illustration purposes only

CASE STYLE: XX211

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



CONTROL LOGIC

RF outputs

2

On

Off

1

Off

On

Control Ports

2

-V

0

1

0

-v

Electrical Specifications

1	FREQ. ⁴ (GHz) INSERTION LOSS (dB) DC-100 100-500 500-1000 1000-2000 MHz MHz MHz MHz The New MHz MHz				1dB COMPR. (dBm)			IN-OUT ISOLATION (dB)														
											DC-100 MHz	100-500 MHz	500-1000 MHz	1000-2000 MHz	DC- Mł		100- Mł		500-1 MH		1000- Mi	
fL		f _u	Тур.	Max.	Тур.	Max.	Тур.	Max.	Тур.	Max.	Тур.	Тур.	Тур.	Тур	Тур.	Min.	Тур.	Min.	Тур.	Min.	Тур.	Min
DC		2.0	0.30	0.8	0.4	0.9	0.50	1.0	0.75	1.3	22	23	24	25	55	50	43	36	34	28	24	20

Addition	nal Specifications					
Control Voltage	-8/0 for compression spec, -8 to -5/0 for all other specs					
Control Current, mA	0.2 max to -8V, 0.0	2 max at 0 to -0.2V				
VSWR(:1)	DC-1GHz	1-2GHz				
	1.2 typ.	1.4 typ.				
Rise/Fall time (10%-90%), ns Switching time, 50% of Control to	4 t	yp.				
90% RF(Turn-on), ns	10 typ					
10% RF(Turn-off), ns	4 typ					
**Video Leakage, mVp-p 0/-5V Control	191	typ.				

21

	**	Video	leakage	or break	through	is defined	as leakage of	switching	sianal to	RF output p	orts.
--	----	-------	---------	----------	---------	------------	---------------	-----------	-----------	-------------	-------

1. RF Power Input(dBm), Max.DC-100MHz100-500MHz500-2000MHz


 Steady State Control 0/-8V 23 27 17

 As a Modulator 11

2. Control Current, 500µA (occurs at -9V to -12V typ)

3. OFF state of RF output is low impedance 4. All RF connections must be DC blocked or held at 0V DC.

Electrical Schematic



Notes

Z


Notes A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp





MSW-2-20+

FREQ. (MHz)	ON INSERTION LOSS (dB) Control @ 0V/-5V)		OFF ISOLATION (dB) Control @ 0V/-5V)				
. ,			IN-OUT	RF IN	RF OUT		
	RF IN-RF OUT	RF IN-RF OUT		(ON PORT			
0.3	0.52	81.93	93.30	1.10	1.11		
1.0	0.52	97.26	97.90	1.10	1.10		
100.0	0.56	59.31	73.94	1.07	1.07		
200.0	0.57	53.23	64.89	1.07	1.07		
300.0	0.57	49.47	58.85	1.07	1.07		
400.0	0.57	46.44	53.61	1.07	1.07		
500.0	0.58	44.05	50.36	1.07	1.06		
600.0	0.58	41.90	47.22	1.07	1.06		
700.0	0.58	39.98	44.58	1.07	1.06		
800.0	0.58	38.20	42.30	1.07	1.07		
900.0	0.58	36.54	40.21	1.06	1.08		
1000.0	0.59	35.06	38.40	1.06	1.09		
1100.0	0.59	33.66	36.75	1.05	1.10		
1200.0	0.59	32.36	35.21	1.04	1.10		
1400.0	0.61	29.98	32.49	1.04	1.11		
1500.0	0.63	28.91	31.14	1.03	1.11		
1600.0	0.66	28.12	29.80	1.03	1.11		
1800.0	0.70	24.70	29.05	1.04	1.12		
1900.0	0.66	22.96	26.48	1.06	1.12		
2000.0	0.64	23.40	25.43	1.06	1.13		

Typical Performance Data







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specification s and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp