

Plug-In

# Power Splitter/Combiner

## PSC-5-1-75+ PSC-5-1-75

5 Way-0° 75Ω 1 to 300 MHz



Generic photo used for illustration purposes only

CASE STYLE: C07

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Maximum Ratings

|   |                |
|---|----------------|
| Operating Temperature   | -55°C to 100°C |
| Storage Temperature   | -55°C to 100°C |
| Power Input (as a splitter)                                     | 1W max.        |
| Internal Dissipation  | 0.5W max.      |
| Permanent damage may occur if any of these limits are exceeded. |                |

### Pin Connections

|             |                |
|-------------|----------------|
| SUM PORT    | 1              |
| PORT 1      | 4              |
| PORT 2      | 8              |
| PORT 3      | 12             |
| PORT 4      | 16             |
| PORT 5      | 15             |
| GROUND      | 2,5,7,11,13,14 |
| CASE GROUND | 2,5,7,11,13,14 |
| NOT USED    | 3,6,9,10       |

### Features

- high isolation, 30 typ.
- excellent amplitude unbalance, 0.3 dB typ.
- rugged welded case

### Applications

- VHF
- signal processing
- instrumentation
- radio communication

### Electrical Specifications

| FREQ. RANGE (MHz)              | ISOLATION (dB) |      |      |      |      |      | INSERTION LOSS (dB) ABOVE 7.0 dB |      |      |      |      |      | PHASE UNBALANCE (Degrees) |      |      | AMPLITUDE UNBALANCE (dB) |      |      |
|--------------------------------|----------------|------|------|------|------|------|----------------------------------|------|------|------|------|------|---------------------------|------|------|--------------------------|------|------|
|                                | L              |      | M    |      | U    |      | L                                |      | M    |      | U    |      | L                         | M    | U    | L                        | M    | U    |
|                                | Typ.           | Min. | Typ. | Min. | Typ. | Min. | Typ.                             | Max. | Typ. | Max. | Typ. | Max. | Max.                      | Max. | Max. | Max.                     | Max. | Max. |
| f <sub>L</sub> -f <sub>U</sub> |                |      |      |      |      |      |                                  |      |      |      |      |      |                           |      |      |                          |      |      |
| 1-300                          | 35             | 20   | 30   | 18   | 25   | 17   | 0.4                              | 0.6  | 0.6  | 0.9  | 0.9  | 1.3  | 2                         | 4    | 8    | 0.2                      | 0.3  | 0.6  |


L = low range [f<sub>L</sub> to 10 f<sub>L</sub>] M = mid range [10 f<sub>L</sub> to f<sub>U</sub>/2] U = upper range [f<sub>U</sub>/2 to f<sub>U</sub>]

### Typical Performance Data

| Freq. (MHz) | Total Loss <sup>1</sup> (dB) |      |      |      |      | Amp. Unbal. (dB) | Isolation (dB) |       |       |       |       | VSWR S | VSWR OUTPUTS |
|-------------|------------------------------|------|------|------|------|------------------|----------------|-------|-------|-------|-------|--------|--------------|
|             | S-1                          | S-2  | S-3  | S-4  | S-5  |                  | 1-2            | 1-3   | 2-3   | 3-5   | 4-5   |        |              |
| 1.00        | 7.40                         | 7.42 | 7.40 | 7.41 | 7.41 | 0.02             | 43.47          | 22.47 | 44.90 | 22.10 | 36.42 | 1.09   | 1.17         |
| 10.00       | 7.24                         | 7.24 | 7.24 | 7.26 | 7.24 | 0.02             | 45.39          | 28.95 | 48.20 | 28.76 | 41.61 | 1.09   | 1.16         |
| 20.00       | 7.27                         | 7.26 | 7.26 | 7.26 | 7.24 | 0.03             | 42.90          | 28.98 | 43.39 | 28.90 | 40.15 | 1.09   | 1.16         |
| 38.40       | 7.29                         | 7.31 | 7.31 | 7.31 | 7.29 | 0.02             | 38.98          | 28.42 | 38.22 | 28.40 | 36.70 | 1.09   | 1.16         |
| 50.00       | 7.30                         | 7.28 | 7.28 | 7.28 | 7.26 | 0.04             | 37.09          | 28.16 | 36.08 | 28.05 | 34.94 | 1.11   | 1.16         |
| 75.80       | 7.33                         | 7.33 | 7.33 | 7.31 | 7.32 | 0.02             | 34.03          | 27.65 | 32.76 | 27.41 | 31.98 | 1.11   | 1.16         |
| 100.00      | 7.33                         | 7.36 | 7.36 | 7.36 | 7.32 | 0.04             | 31.90          | 27.11 | 30.52 | 26.76 | 29.91 | 1.12   | 1.16         |
| 122.50      | 7.38                         | 7.40 | 7.40 | 7.38 | 7.33 | 0.07             | 30.46          | 26.74 | 29.03 | 26.22 | 28.45 | 1.14   | 1.15         |
| 150.50      | 7.37                         | 7.45 | 7.45 | 7.43 | 7.33 | 0.08             | 29.11          | 26.37 | 27.60 | 25.63 | 27.00 | 1.15   | 1.16         |
| 178.50      | 7.42                         | 7.54 | 7.51 | 7.49 | 7.39 | 0.15             | 28.00          | 25.99 | 26.43 | 25.11 | 25.82 | 1.16   | 1.16         |
| 200.00      | 7.45                         | 7.57 | 7.56 | 7.49 | 7.42 | 0.15             | 27.36          | 25.83 | 25.73 | 24.78 | 25.13 | 1.17   | 1.16         |
| 225.30      | 7.47                         | 7.65 | 7.60 | 7.55 | 7.43 | 0.22             | 26.73          | 25.72 | 25.08 | 24.54 | 24.42 | 1.17   | 1.18         |
| 253.30      | 7.56                         | 7.74 | 7.69 | 7.66 | 7.49 | 0.25             | 26.21          | 25.80 | 24.49 | 24.36 | 23.75 | 1.18   | 1.20         |
| 281.30      | 7.62                         | 7.84 | 7.78 | 7.69 | 7.51 | 0.33             | 25.80          | 26.02 | 23.98 | 24.34 | 23.22 | 1.18   | 1.21         |
| 300.00      | 7.67                         | 7.91 | 7.82 | 7.75 | 7.55 | 0.36             | 25.54          | 26.27 | 23.67 | 24.38 | 22.87 | 1.19   | 1.23         |




1. Total Loss = Insertion Loss + 7dB splitter loss.

### Outline Drawing




### Outline Dimensions (inch/mm)

| A     | B     | C    | D     | E    | F    | G    | H    | wt    |
|-------|-------|------|-------|------|------|------|------|-------|
| .770  | .810  | .380 | .410  | .030 | .200 | .20  | .14  | grams |
| 19.56 | 20.57 | 9.65 | 10.41 | 0.76 | 5.08 | 5.08 | 3.56 | 11.0  |



### electrical schematic



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

