


Low Pass Filter

RLPF-EDU1086

Surface Mount

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.


CASE STYLE : CK605

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C

| Parameter | Min. | Typ. | Max. | Units |
|-----------------------------|-------|------|------|-------|
| Passband (Loss < 2.5 dB) | DC | | 1800 | MHz |
| Insertion loss 3dB | | 1850 | | MHz |
| Stopband (Loss > 20 dB) | @2075 | | | MHz |
| (Loss > 25 dB) | 2100 | | 4000 | MHz |
| Passband VSWR | | 1.4 | 2.1 | (:1) |
| Stopband VSWR | | 20 | | (:1) |

Functional Schematic

| MAXIMUM RATINGS | |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C |
| Storage Temperature | -55°C to 100°C |
| RF Power Input | 10mW |



PIN CONNECTIONS

| | |
|---------------|--------------------------------|
| Input | 2 |
| Output | 10 |
| Not Connected | 14 |
| Case Ground | 1,3,4,5,6,7,8,9,11,12,13,15,16 |