

Non-Catalog Model

Frequency Mixer


SBL-173SH

Level 17 (LO Power +17 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : A06

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	5		1200	MHz
	RF (fL to fU)	5		1200	MHz
	IF	1		1200	MHz
Conversion Loss	mid band		5.7	7.0	dB
	Total Range			8.5	dB
LO-RF Isolation	Low Range	35	40		dB
	Mid Range	25	35		dB
	Upper Range	20	35		dB
LO-IF Isolation	Low Range	35	40		dB
	Mid Range	20	35		dB
	Upper Range	20	30		dB
IP3 Input		+27.5	+30		dBm
1 dB Comp. Input Power			+14		dBm

Notes: Low Range = [fL to 10fL] Mid Range = [10fL to fU/2] Upper Range = [fU/2 to fU]
 mid band = [2fL to fU/2]

IP3 : RF Power = 0 dBm @ 200 MHz & 202 MHz , LO Power = +17 dBm @ 180 MHz
 Non-hermetic

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA

PIN CONNECTIONS	
LO	8
RF	1
IF	3, 4 ^
GROUND	2, 5, 6, 7

^ - pins must be connected together externally

Electrical Schematics

