

2 Way-0° 50Ω 1600 to 2000 MHz



CASE STYLE: SM1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	2W max.
Internal Dissipation	0.125W max.

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

SUM PORT	3
PORT 1	10
PORT 2	6
GROUND	1,2,4,5,7,8,9

Outline Drawing



PCB Land Pattern




Suggested Layout,
Tolerance to be within ±.002
ADJACENT GROUND PINS SHALL BE CONNECTED TO EACH OTHER AND TO GROUND PAD

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H		
.250	.300	.070	.290	.050	.015	.050	.060		
6.35	7.62	1.78	7.37	1.27	0.38	1.27	1.52		
J	K	L	M	N	P	Q	R	wt	
.030	.080	.300	.100	.020	.015	.070	.014	grams	
0.76	2.03	7.62	2.54	0.51	0.38	1.78	0.36	0.3	

Demo Board MCL P/N: TB-95 Suggested PCB Layout (PL-070)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- low insertion loss, 0.4 dB typ.
- low amplitude unbalance, 0.25 dB typ.
- leads for excellent solderability and strain relief
- aqueous washable
- protected by U.S Patent, 5,534,830

Applications

- PCS/DCS




Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 3.0 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)
	Typ.	Min	Typ.	Max.	Max.	Max.
f_L - f_U						
1600-2000	19	13	0.4	1.0	6.0	0.6

Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
1600	3.52	3.28	0.25	21.63	2.95	1.39	1.26	1.23
1650	3.51	3.28	0.24	21.64	3.06	1.37	1.26	1.22
1675	3.55	3.30	0.25	21.57	3.18	1.36	1.26	1.22
1700	3.50	3.25	0.25	21.38	3.36	1.35	1.26	1.21
1750	3.54	3.29	0.25	20.50	3.30	1.35	1.25	1.20
1775	3.55	3.28	0.26	20.17	3.52	1.35	1.24	1.20
1800	3.47	3.23	0.25	19.65	3.71	1.35	1.24	1.19
1825	3.51	3.28	0.24	19.01	3.59	1.35	1.24	1.19
1850	3.57	3.31	0.27	18.55	3.77	1.36	1.23	1.18
1875	3.52	3.26	0.26	18.14	4.00	1.36	1.23	1.17
1900	3.50	3.27	0.23	17.55	3.98	1.37	1.23	1.16
1925	3.56	3.31	0.25	16.98	3.98	1.38	1.23	1.15
1950	3.55	3.31	0.26	16.55	4.19	1.40	1.22	1.14
1975	3.53	3.30	0.24	16.13	4.24	1.41	1.22	1.14
2000	3.58	3.34	0.26	15.63	4.27	1.42	1.21	1.13

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic

