

Non-Catalog Model

Frequency Mixer

SBL-3LH+

Level 10 (LO Power +10 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



CASE STYLE : A06

Please click "Back", and then click "Contact Us" for Applications support.

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	0.07		250	MHz
	RF (fL to fU)	0.07		250	MHz
	IF	0		250	MHz
Conversion Loss	mid band		4.9	7.0	dB
	Total Range			8.5	dB
LO-RF Isolation	Low Range	45	60		dB
	Mid Range	35	60		dB
	Upper Range	30	45		dB
LO-IF Isolation	Low Range	35	57		dB
	Mid Range	30	53		dB
	Upper Range	25	42		dB
1 dB Comp. Input Power			+5		dBm

Notes: Low Range = [fL to 10fL] Mid Range = [10fL to fU/2] Upper Range = [fU/2 to fU]
 mid band = [2fL to fU/2]

Non-hermetic

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	8
RF	1
IF	3, 4 ^
GROUND	2, 5, 6, 7

^ - pins must be connected together externally

Electrical Schematics

