

# Frequency Synthesizer

SSN-3132A-119+

50Ω 2932 to 3132 MHz

## The Big Deal

- Fractional N synthesizer
- Low phase noise and spurious
- Very small size 0.60" x 0.60" x 0.138"



CASE STYLE: KJ1367

## Product Overview

The SSN-3132A-119+ is a Frequency Synthesizer, designed to operate from 2932 to 3132 MHz for WiMAX application. The SSN-3132A-119+ is packaged in a metal case (size of 0.60" x 0.60" x 0.138") to shield against unwanted signals and noise.

## Key Features

Feature	Advantages
Low phase noise and spurious: <ul style="list-style-type: none"><li>• Phase Noise: -95 dBc/Hz typ. @ 10 kHz offset</li><li>• Step Size Spurious: -94 dBc typ.</li><li>• Comparison Spurious: -83 dBc typ.</li><li>• Reference Spurious: -83 dBc typ.</li></ul>	Low phase noise and spurious improve system EVM (Error Vector Magnitude).
Robust design and construction	To enhance the robustness of SSN-3132A-119+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.
Small size, 0.60" x 0.60" x 0.138"	The small size enables the SSN-3132A-119+ to be used in compact designs.

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)

# Frequency Synthesizer

SSN-3132A-119+

50Ω 2932 to 3132 MHz

## Features

- Fractional N synthesizer
- Integrated VCO + PLL
- Low phase noise and spurious
- Robust design and construction
- Low operating voltage (VCC VCO=+4.85V, VCC PLL=+3.2V)
- Small size 0.60" x 0.60" x 0.138"



CASE STYLE: KJ1367

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


## Applications

- WiMAX

## General Description

The SSN-3132A-119+ is a Frequency Synthesizer, designed to operate from 2932 to 3132 MHz for WiMAX application. The SSN-3132A-119+ is packaged in a metal case (size of 0.60" x 0.60" x 0.138") to shield against unwanted signals and noise. To enhance the robustness of SSN-3132A-119+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.

## Simplified Schematic



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



**Electrical Specifications** (over operating temperature -40°C to +85°C)

Parameters	Test Conditions	Min.	Typ.	Max.	Units	
Frequency Range	-	2932	-	3132	MHz	
Step Size	-	-	250	-	kHz	
Comparison Frequency	-	-	26	-	MHz	
Settling Time	Within ± 1 kHz	-	9	-	mSec	
Output Power	-	0	+2.5	+6.0	dBm	
SSB Phase Noise	@ 100 Hz offset	-	-74	-	dBc/Hz	
	@ 1 kHz offset	-	-88	-83		
	@ 10 kHz offset	-	-95	-90		
	@ 100 kHz offset	-	-119	-113		
	@ 1 MHz offset	-	-140	-134		
Integrated SSB Phase Noise	@1kHz to 10MHz	-	-50	-	dBc	
Step Size Spurious Suppression	Step Size 250 kHz	-	-94	-70	dBc	
0.5 Step Size Spurious Suppression	0.5 Step Size 125 kHz	-	-84	-60		
Reference Spurious Suppression	Ref. Freq. 52 MHz	-	-83	-74		
Comparison Spurious Suppression	Comp. Freq. 26 MHz	-	-83	-75		
Non - Harmonic Spurious Suppression	-	-	-90	-		
Harmonic Suppression	-	-	-27	-17		
VCO Supply Voltage	+4.85	+4.75	+4.85	+5.25	V	
PLL Supply Voltage	+3.20	+3.10	+3.20	+3.30	V	
VCO Supply Current	-	-	44	51	mA	
PLL Supply Current	-	-	16	24		
Reference Input (External)	Frequency	52 (square wave)	-	52	MHz	
	Amplitude	1	-	1	V <sub>P-P</sub>	
	Input impedance	-	-	100	KΩ	
	Phase Noise @ 1 kHz offset	-	-	-130	dBc/Hz	
RF Output port Impedance	-	-	50	-	Ω	
Input Logic Level	Input high voltage	-	2.65	-	V	
	Input low voltage	-	-	0.60	V	
Digital Lock Detect	Locked	-	2.70	-	3.70	V
	Unlocked	-	-	-	0.40	V
Frequency Synthesizer PLL	-	ADF4153				
PLL Programming	-	3-wire serial 3.2V CMOS				
Register Map @ 3132 MHz	R0_Register	-	(MSB) 11110000000011000000 (LSB)			
	R1_Register	-	(MSB) 101001000000110100001 (LSB)			
	R2_Register	-	(MSB) 1111100010 (LSB)			
	R3_Register	-	(MSB) 1111000111 (LSB)			

**Absolute Maximum Ratings**

Parameters	Ratings
VCO Supply Voltage	5.8V
PLL Supply Voltage	4.0V
VCO Supply Voltage to PLL Supply Voltage	-0.3V to +5.8V
Reference Frequency Voltage	-0.3Vmin, VCC PLL +0.3Vmax
Data, Clock, LE Levels	-0.3Vmin, VCC PLL +0.3Vmax
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

Permanent damage may occur if any of these limits are exceeded

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Typical Performance Data

FREQUENCY (MHz)	POWER OUTPUT (dBm)			VCO CURRENT (mA)			PLL CURENT (mA)		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
2932	2.85	2.75	2.79	42.17	43.78	45.22	14.74	15.83	18.08
2944	2.62	2.59	2.62	42.20	43.80	45.24	14.69	15.78	18.04
2966	2.25	2.39	2.23	42.25	43.87	45.29	14.44	15.52	17.76
2988	2.48	2.45	2.27	42.34	43.93	45.36	14.50	15.59	17.84
3010	2.71	2.73	2.57	42.40	43.99	45.42	14.74	15.85	18.10
3032	2.65	2.68	2.58	42.43	44.02	45.45	14.86	15.97	18.24
3054	2.50	2.46	2.51	42.45	44.05	45.47	14.96	16.08	18.35
3076	2.15	2.32	2.21	42.50	44.10	45.51	14.75	15.86	18.12
3098	2.03	2.23	2.00	42.57	44.16	45.57	14.56	15.66	17.90
3120	2.64	2.52	2.28	42.64	44.21	45.61	12.71	13.71	15.90
3132	2.78	2.68	2.60	42.66	44.23	45.64	14.96	16.07	18.34

FREQUENCY (MHz)	HARMONICS (dBc)					
	F2			F3		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
2932	-25.45	-26.52	-29.28	-37.06	-35.69	-40.56
2944	-26.50	-27.59	-29.00	-36.67	-37.51	-43.79
2966	-25.33	-26.75	-27.29	-39.61	-36.90	-42.67
2988	-23.58	-24.18	-28.90	-38.46	-38.80	-44.96
3010	-26.88	-27.25	-27.30	-39.96	-41.57	-53.34
3032	-22.77	-25.80	-26.84	-42.64	-45.76	-58.30
3054	-25.91	-25.23	-29.23	-48.69	-51.57	-55.03
3076	-25.33	-24.61	-27.24	-45.11	-50.41	-46.65
3098	-23.54	-24.99	-24.34	-46.86	-48.51	-43.34
3120	-23.96	-28.23	-30.18	-47.59	-48.29	-42.60
3132	-24.05	-25.40	-25.61	-43.68	-47.77	-42.04

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	+25°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
2932	-78.59	-88.09	-95.53	-118.24	-139.32
2944	-77.70	-90.62	-95.84	-118.30	-139.40
2966	-77.97	-88.64	-95.82	-118.70	-139.81
2988	-78.21	-88.97	-95.64	-118.90	-139.87
3010	-80.68	-87.99	-95.25	-119.16	-140.14
3032	-78.45	-88.41	-95.26	-119.20	-140.14
3054	-77.87	-87.52	-94.91	-118.99	-139.68
3076	-78.01	-86.88	-95.31	-118.98	-139.67
3098	-77.98	-89.12	-95.04	-118.96	-139.77
3120	-76.86	-88.70	-95.51	-118.69	-139.87
3132	-77.34	-90.38	-94.77	-118.67	-139.79

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	-45°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
2932	-80.08	-89.83	-97.48	-118.80	-140.28
2944	-78.70	-88.02	-97.39	-119.02	-140.47
2966	-76.97	-89.61	-97.02	-119.16	-140.73
2988	-76.02	-90.04	-97.05	-119.59	-141.03
3010	-77.60	-89.37	-96.26	-119.90	-141.23
3032	-78.20	-88.62	-96.99	-119.77	-141.13
3054	-76.05	-87.75	-96.50	-119.66	-140.88
3076	-75.94	-89.47	-95.52	-119.88	-141.12
3098	-76.63	-89.15	-95.95	-119.85	-141.21
3120	-80.70	-88.41	-96.18	-119.86	-141.62
3132	-78.69	-87.43	-96.15	-119.85	-141.13

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	+85°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
2932	-81.24	-90.08	-95.60	-117.30	-138.31
2944	-81.00	-89.78	-95.69	-117.40	-138.26
2966	-77.86	-89.05	-95.53	-117.63	-138.41
2988	-81.08	-88.67	-95.17	-117.78	-138.70
3010	-76.59	-89.65	-94.89	-117.80	-138.80
3032	-77.75	-87.98	-95.28	-117.69	-138.51
3054	-83.61	-89.16	-94.73	-117.60	-138.48
3076	-78.29	-89.55	-94.20	-117.42	-138.38
3098	-79.24	-89.10	-94.49	-117.31	-138.29
3120	-79.63	-88.39	-93.78	-117.25	-138.06
3132	-78.68	-89.46	-93.21	-117.22	-138.10

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



COMPARISON SPURIOUS ORDER	COMPARISON SPURIOUS @Fcarrier 2932MHz+(n*Fcomparison) (dBc) note 1			COMPARISON SPURIOUS @Fcarrier 3032MHz+(n*Fcomparison) (dBc) note 1			COMPARISON SPURIOUS @Fcarrier 3132MHz+(n*Fcomparison) (dBc) note 1		
	n			n			n		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
-5	-82.34	-83.86	-85.22	-83.66	-84.86	-86.32	-83.79	-84.76	-86.07
-4	-83.03	-82.47	-82.65	-84.67	-84.36	-84.90	-84.42	-84.45	-86.23
-3	-86.68	-89.13	-87.83	-88.72	-89.78	-87.96	-89.82	-88.11	-88.57
-2	-88.37	-86.62	-87.37	-89.27	-88.57	-87.26	-88.73	-90.43	-89.30
-1	-90.97	-88.15	-91.88	-88.44	-87.79	-91.18	-88.46	-87.20	-84.64
0 <sup>note 2</sup>	-	-	-	-	-	-	-	-	-
+1	-91.28	-88.86	-91.20	-90.24	-90.64	-93.60	-89.31	-88.57	-86.51
+2	-88.06	-88.16	-88.29	-90.56	-89.69	-88.33	-95.24	-94.13	-91.15
+3	-87.90	-88.85	-87.68	-88.02	-88.75	-88.81	-89.09	-87.78	-88.70
+4	-82.48	-82.53	-83.22	-83.75	-83.82	-84.38	-84.42	-84.63	-85.21
+5	-83.11	-84.96	-86.31	-83.70	-85.22	-86.47	-83.61	-84.75	-86.27

Note 1: Comparison frequency 26 MHz  
 Note 2: All spurs are referenced to carrier signal (n=0).

REFERENCE SPURIOUS ORDER	REFERENCE SPURIOUS @Fcarrier 2932MHz+(n*Freference) (dBc) note 3			REFERENCE SPURIOUS @Fcarrier 3032MHz+(n*Freference) (dBc) note 3			REFERENCE SPURIOUS @Fcarrier 3132MHz+(n*Freference) (dBc) note 3		
	n			n			n		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
-5	-98.13	-102.48	-101.21	-98.23	-102.07	-112.10	-99.99	-101.70	-105.05
-4	-93.90	-91.25	-93.34	-97.84	-96.05	-97.70	-99.72	-99.91	-98.79
-3	-84.80	-84.55	-86.36	-87.01	-87.71	-88.14	-88.32	-89.21	-88.90
-2	-83.01	-82.53	-82.67	-84.60	-84.28	-85.00	-84.32	-84.52	-86.22
-1	-88.44	-86.66	-87.30	-89.24	-88.53	-87.51	-88.68	-90.45	-89.21
0 <sup>note 4</sup>	-	-	-	-	-	-	-	-	-
+1	-88.04	-88.25	-88.30	-90.33	-89.64	-88.48	-95.27	-93.91	-91.04
+2	-82.44	-82.55	-83.20	-83.67	-83.76	-84.41	-84.31	-84.61	-85.25
+3	-85.22	-85.63	-86.85	-88.12	-87.73	-87.90	-89.07	-89.34	-89.18
+4	-94.88	-94.72	-95.04	-100.52	-98.28	-97.71	-102.04	-101.37	-98.53
+5	-108.57	-125.31	-107.83	-102.62	-107.58	-109.29	-102.04	-105.90	-107.96

Note 3: Reference frequency 52 MHz  
 Note 4: All spurs are referenced to carrier signal (n=0).

Notes  
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



STEP SIZE SPURIOUS ORDER n	0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 2932MHz+(n*Fstep size) (dBc) note 5			0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 3032MHz+(n*Fstep size) (dBc) note 5			0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 3132MHz+(n*Fstep size) (dBc) note 5		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
-5.0	-114.54	-107.64	-117.28	-113.24	-108.76	-117.85	-114.84	-110.85	-115.82
-4.5	-113.45	-116.41	-109.64	-114.54	-115.33	-118.44	-117.02	-119.32	-113.45
-4.0	-112.95	-113.33	-112.95	-112.58	-116.86	-115.43	-107.90	-108.90	-108.85
-3.5	-108.68	-111.10	-114.25	-112.69	-115.31	-111.17	-115.64	-114.83	-116.57
-3.0	-113.18	-105.57	-109.62	-115.06	-112.22	-113.90	-114.94	-112.18	-111.55
-2.5	-106.55	-106.14	-105.82	-111.52	-104.89	-110.85	-112.45	-112.21	-113.20
-2.0	-102.58	-104.28	-109.84	-107.76	-108.04	-111.24	-107.04	-107.91	-105.90
-1.5	-96.69	-102.67	-104.07	-107.66	-98.84	-105.33	-103.32	-98.76	-103.36
-1.0	-94.22	-95.76	-97.93	-96.13	-101.58	-96.14	-97.04	-100.30	-95.51
-0.5	-81.90	-84.93	-86.18	-84.87	-84.28	-82.02	-86.13	-83.53	-86.67
0 <sup>note 6</sup>	-	-	-	-	-	-	-	-	-
+0.5	-80.95	-84.83	-84.82	-87.56	-84.49	-81.29	-84.19	-86.23	-85.17
+1.0	-92.94	-97.89	-94.98	-95.68	-95.11	-96.08	-97.64	-96.48	-99.00
+1.5	-96.25	-104.54	-106.50	-103.69	-102.07	-106.58	-106.08	-102.12	-100.26
+2.0	-102.96	-105.84	-109.21	-107.12	-105.97	-107.70	-106.64	-107.31	-107.90
+2.5	-102.43	-101.67	-107.28	-110.29	-103.00	-109.57	-111.07	-115.02	-113.54
+3.0	-111.47	-105.76	-111.86	-115.42	-113.50	-112.14	-112.65	-111.24	-111.90
+3.5	-110.36	-110.63	-112.33	-116.61	-113.18	-116.71	-114.52	-112.76	-111.33
+4.0	-117.38	-116.41	-117.76	-114.32	-117.35	-114.52	-109.15	-108.70	-108.50
+4.5	-114.30	-114.59	-113.60	-115.48	-116.16	-113.71	-118.09	-112.96	-119.16
+5.0	-115.48	-109.82	-113.34	-120.04	-114.97	-112.64	-110.16	-112.81	-108.40

Note 5: Step size 250 kHz




Note 6: All spurs are referenced to carrier signal (n=0).

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Typical Performance Curves








Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)













Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)








Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)






Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Pin Configuration




Pin Connection

Pin Number	Function
1	CLOCK
2	DATA
3	ENABLED
4	REF IN
5	GND
6	GND
7	VCC VCO
8	GND
9	RF OUT
10	GND
11	LOCK DET
12	VCC PLL

Recommended Application Circuit

Note: REF IN and RF OUT ports are internally AC coupled.




Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



**Device Marking**



**Additional Detailed Technical Information**

Additional information is available on our web site. To access this information enter the model number on our web site home page.

**Case Style:** KJ1367

**Tape & Reel:** TR-F95

**Suggested Layout for PCB Design:** PL-317

**Evaluation Board:** TB-552+

**Environment Ratings:** ENV65T2

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

