Bandpass Filter

SXBP-176+

 50Ω 175 to 177 MHz

- Narrow band flat group delay response
- Wide stopband rejection, 40 dB
- Good matching, (VSWR 1.3:1 typical)
- Miniature shielded package



CASE STYLE: HF1139

Product Overview

The SXBP-176+ is a cross coupled design, narrow-band bandpass filter fabricated using SMT technology. Covering 176 MHz ± 1 MHz band width, these units offer good matching within the passband and high rejection. This unit uses a miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across production lots and consistent performance across temperature.

Key Features

| Narrow-band bandpass filter with flat group delay | This helps in excellent adjacent channel rejection and minimum signal distortion. |
|---|---|
| More than 40dB rejection up to 1000 MHz | This enables the filter to attenuate spurious signals and reject harmonics for broad band of frequency. |
| Small size, 0.44" x 0.74" x .27" | The surface mount package enables the SXBP-176+ to be used in compact designs. |

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

Bandpass Filter

50Q 175 to 177 MHz

SXBP-176+



CASE STYLE: HF1139


Features

- · Narrow band flat group delay
- Good VSWR, 1.3:1 Typical
- High Rejection, 40 dB
- Shielded case
- Aqueous washable


Applications

- · Harmonic Rejection
- Transmitters / Receivers
- Military

Functional Schematic



Typical Frequency Response



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C


| Parameter | | F# | Frequency (MHz) | Min. | Тур. | Max. | Unit |
|------------------|------------------|-------|-----------------|------|------|------|------|
| | Center Frequency | _ | _ | _ | 176 | _ | MHz |
| Pass Band | Insertion Loss | F1-F2 | 175-177 | _ | 3.3 | 4.8 | dB |
| | VSWR | F1-F2 | 175-177 | _ | 1.3 | 1.5 | :1 |
| Stop Band, Lower | Insertion Loss | DC-F3 | DC-155 | 20 | 30 | _ | dB |
| | VSWR | DC-F3 | DC-155 | _ | 15 | _ | :1 |
| Stop Band, Upper | Insertion Loss | F4-F5 | 199-1000 | 20 | 31 | _ | dB |
| | VSWR | F4-F5 | 199-1000 | _ | 11 | _ | :1 |


| Maximum Ratings | | | | |
|-----------------------|----------------|--|--|--|
| Operating Temperature | -40°C to 85°C | | | |
| Storage Temperature | -55°C to 100°C | | | |
| RF Power Input | 0.25W max. | | | |


Permanent damage may occur if any of these limits are exceeded


Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) | Frequency (MHz) | Group Delay (nsec) |
|--------------------|------------------------|--------------|--------------------|-----------------------|
| 1.0 | 93.62 | 1737.18 | 175.00 | 43.54 |
| 143.0 | 51.62 | 96.51 | 175.10 | 44.08 |
| 155.0 | 32.29 | 36.97 | 175.20 | 43.90 |
| 160.0 | 22.86 | 19.98 | 175.30 | 43.69 |
| 164.0 | 14.07 | 8.86 | 175.40 | 43.71 |
| 167.0 | 7.57 | 3.49 | 175.60 | 43.60 |
| 175.0 | 3.21 | 1.21 | 175.70 | 43.54 |
| 176.0 | 3.21 | 1.22 | 175.80 | 42.95 |
| 177.0 | 3.24 | 1.25 | 175.90 | 43.43 |
| 185.0 | 6.30 | 3.52 | 176.00 | 43.35 |
| 190.0 | 12.52 | 9.53 | 176.10 | 42.97 |
| 199.0 | 31.10 | 32.79 | 176.20 | 43.18 |
| 200.0 | 33.03 | 36.20 | 176.30 | 43.28 |
| 205.0 | 41.84 | 51.10 | 176.40 | 43.21 |
| 209.0 | 48.28 | 62.05 | 176.50 | 43.00 |
| 300.0 | 62.65 | 217.15 | 176.60 | 43.24 |
| 500.0 | 65.17 | 82.73 | 176.70 | 43.19 |
| 750.0 | 56.76 | 69.49 | 176.80 | 43.22 |
| 800.0 | 55.56 | 78.97 | 176.90 | 42.84 |
| 1000.0 | 53.36 | 56.04 | 177.00 | 42.96 |









A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.ninicircuits.com/MCLStore/terms.jsp


Pad Connections

| INPUT | 1 |
|--------|-------------|
| OUTPUT | 8 |
| GROUND | 2,3,4,5,6,7 |


Demo Board MCL P/N: TB-368 Suggested PCB Layout (PL-230)



- 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



Outline Drawing



Outline Dimensions (inch)

| Α | В | С | D | Ε | F | G |
|-------|-------|-------|------|------|------|-------|
| .44 | .74 | .27 | .200 | .07 | .060 | .040 |
| 11.18 | 18.80 | 6.86 | 5.08 | 1.78 | 1.52 | 1.02 |
| Н | J | K | L | М | | wt |
| .660 | .200 | .470 | .055 | .060 | | grams |
| 16 76 | 5.08 | 11 94 | 1 40 | 1 52 | | 3.0 |

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.ninicircuits.com/MCLStore/terms.jsp

