# **USB Synthesized Signal Generator**

**SSG-4000HP** 

 $50\Omega$  -50 dBm to +20 dBm. 250-4000 MHz

# **The Big Deal**

- High output power (+20 dBm max)
- 70 dB Adjustable output power range
- Internal & External pulse modulation
- Cost effective Signal Generator



Case Style: LV1754

#### **Product Overview**

Mini-Circuits SSG-4000HP is a wideband synthesized signal generator operating over a frequency range of 250 to 4000 MHz. The signal generator is cased in a rugged metal shielded package ( $8.37^{\circ}$  x  $8.5^{\circ}$  x  $2.15^{\circ}$ ) and equipped with an N-type  $50\Omega$  connector at the RF output port.

The signal generator is supplied with a CD containing user friendly GUI control software and programming APIs for 32 and 64 bit environments. Using the supplied software, the user can easily select one of several different output modes including multiple pulse modulation options, frequency sweep, and power sweep (up, down, or bidirectional).

The SSG-4000HP can be controlled from almost any Windows or Linux PC, via USB 2.0 interface. Included with the generator are a 2.7 ft. USB cable and a 24V power adapter. Longer USB cables and a mounting bracket are available as additional options.

## **Key Features**

Feature	Advantages
Wide output power dynamic range	Dynamic range 70 dB, output power from -50dBm to +20dBm in 0.25dB steps
USB HID (Human Interface Device)	Plug-and-Play (no need to install a driver for the device).
Pulse modulation options	The SSG-4000HP can produce pulse modulated RF using internal or external modulating signal
Multiple sweep options	The SSG-4000HP can be set to sweep either power or frequency up, down, or bidirectionally.
Software CD with program instructions for various operating systems	The unit is supplied with a CD containing a user friendly Graphical User Interface (GUI) control program and API objects for Windows <sup>®</sup> operating systems. Programming instructions are included for 32 and 64 bit versions of Linux <sup>®</sup> and Windows <sup>®</sup> operating systems. The SSG-6001RC is compatible with LabVIEW <sup>®</sup> , Delphi <sup>®</sup> , C++, C#, Visual Basic <sup>®</sup> , .NET software and more; for other operating environments and languages please contact our applications department for support.

<u>Trademarks:</u> Windows is a registered trademark of Microsoft Corporation in the United States and other countries. Linux is a registered trademark of Linus Torvalds. Pentium is a registered trademark of Intel Corporation. Neither Mini-Circuits nor the Mini-Circuits SSG-series Synthesized Signal Generators are affiliated with or endorsed by the owners of the above referenced trademarks

Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation.



# **USB Synthesized Signal Generator**

 $50\Omega$  -50 dBm to +20 dBm, 250-4000 MHz

#### **Features**

- High power output (+20 dBm max)
- Adjustable output power, 70 dB dynamic range
- USB HID control interface (Plug and Play)
- · Small, light weight
- Power and/or frequency sweep options
- Multiple pulse modulation options (external, free run, triggered)
- Separate Trigger In and Trigger Out ports
- · Easy installation and operation
- User friendly Windows® Graphical User Interface
- Supports a wide range of programming environments (See application note <u>AN-49-001</u> for details)
- Mounting bracket (Optional)



# **SSG-4000HP**

#### **Included Accessories**


Model No.	Description	Qty.
AC/DC-24-3W1	AC/DC 24V adapter (see Ordering Information)	1
CBL-3W1-XX	AC power cord (see Ordering Information)	1
USB-CBL-AB-3+	2.7ft. USB cable	1
SSG-CD	Software CD	1

RoHS Compliant
See our web site for RoHS Compliance
methodologies and qualifications

#### **Applications**

- Lab Test equipment
- · Automated Test capability
- · Production line testing
- · Field testing

#### Mini-Circuits Control Program for USB Synthesized Signal Generators



Electrical Specifications (General RF) at +25°C

Parameter	Test Conditions	Min.	Тур.	Max.	Units	
Output Frequency	-	250	-	4000	MHz	
Frequency Resolution	-	5	_	-	kHz	
Frequency accuracy Using Internal Reference		_	±1	_	ppm	
Settling time 1,3	-	-	2.5	-		
Minimum Dwell Time <sup>2,3</sup>	-	-	10	-	msec	
VSWR	250 - 3000 MHz	-	1.5	-		
VSWH	3000 - 4000 MHz	-	1.3	-	:1	
O	250 - 3200 MHz	+20	+21.5	-		
Output power Max <sup>5</sup>	3200 - 4000 MHz	Note 4	+19	-	dBm	
Output power Min <sup>5</sup>	250 - 4000 MHz	250 - 4000 MHz – –		-50		
Power resolution (nom.)	on (nom.)		0.25	_	dB	
Dynamic range	-	_	70	-	dB	
Output power accuracy	-	_	±0.25	±1.00	dB	
RF output level	@RF OFF	_	-95	-	dBm	
	PWR <sub>out</sub> = -50 dBm	-	-43	-		
	PWR <sub>out</sub> = -30 dBm	-	-61	-		
Harmonics & Sub-Harmonics	PWR out= 0 dBm	-	-46	-	dBc	
	PWR <sub>out</sub> +10 dBm	_	-45	-		
	PWR <sub>out</sub> +15 dBm	-	-38	-		
	@Frequency step size = 5 kHz	-	-50	-		
Nen Harmania Cauriaua 6	@Frequency step size = 100 kHz	-	-63	-	dDa	
Non-Harmonic Spurious <sup>6</sup>	@Frequency step size = 1 MHz	-	-80	-	dBc	
	@Frequency step size= 10 MHz	-	-90	-		

## Typical Phase Noise, SSB <sup>6</sup> (dBc/Hz) at +25°C

Carrier		Frequency Offset									
Frequency (MHz)	100	100 Hz		1 kHz		10 kHz		100 kHz		1 MHz	
	Lowest Spurs	Lowest Noise	Lowest Spurs	Lowest Noise	Lowest Spurs	Lowest Noise	Lowest Spurs	Lowest Noise	Lowest Spurs	Lowest Noise	
250	-94	-96	-102	-111	-102	-107	-120	-123	-147	-147	
1060	-81	-83	-91	-98	-91	-94	-110	-112	-139	-139	
2600	-74	-76	-82	-90	-82	-87	-102	-106	-132	-133	
4000	-69	-72	-79	-87	-81	-88	-101	-106	-131	-132	

<sup>&</sup>lt;sup>1</sup> Settling time - transition between two signals during which generator is in RF OFF state.

<sup>&</sup>lt;sup>2</sup> Dwell time - duration of each signal point in a Sweep or Hop sequence set by user. Default is minimum dwell time.

<sup>&</sup>lt;sup>3</sup> Generator response time is Dwell time + Settling Time.

<sup>&</sup>lt;sup>4</sup> Max available power out degrades over the 3200-4000 MHz range to +17 dBm

<sup>&</sup>lt;sup>5</sup> The generator is calibrated within typical power range, however performance is guaranteed only within power max/min limits.

<sup>&</sup>lt;sup>6</sup> It is recommended to work in Lowest Spur mode when using frequency step size of up to 50 kHz and Lowest Noise mode for frequency step size greater than 50kHz. Working in Lowest Spur or Lowest Noise mode outside the recommended range may cause excessive Noise (in Lowest Spur mode) or excessive spurs (in Lowest Noise mode)

## Electrical Specifications (Pulse modulation modes) <sup>6</sup> at +25°C

Parameter	Test Conditions	Test Conditions			Max.	Units	
Date - Mish	Naminalization	Internal Pulse source	1	-	_	11800	
Pulse Width	Nominal value	External Pulse source	10	-	_	μSec	
Pulse Period	Measured at the 50% poir	nts	2 μSec		10 Sec	-	
Duty cycle (in Free Run)	Pulse Width divided by Pu	ılse Period	0.01		99.99	%	
Rise / Fall time	Measured between 10% a	and 90%	-	35 / 45	-	nSec	
Pulse Width Accuracy	Measured at 50% of pulse external modulation	e level for Internal and	-	±2	-	%	
External pulse mod. input threshold	External pulse modulation	1	_	-	2.4	٧	
Trianger reconnected delay.	Trigger edge to 50% of	Internal Pulse source 7	_	3.5	_	С.	
Trigger response delay	pulse level	External Pulse source	-	0.8	-	μSec	
Pulse Power ratio	@PWR <sub>OUT</sub> =+20dBm, FRI	EQ <sub>OUT</sub> =250 MHz	_	60	_	dD	
Pulse Power ratio	@PWR <sub>OUT</sub> =+17dBm, FRI	EQ <sub>OUT</sub> =4000 MHz	-	45	_	dB	

<sup>6</sup> Pulse mode is supported from Firmware Rev. B3 external pulse source from Firmware Rev. C7. Firmware from Rev. B1 onwards can be upgraded using the latest software CD (available for download from http://www.minicircuits.com/support/software\_download.html

#### Electrical Specifications at +25°C (Reference, Trigger & DC power)

Parameter		Test Conditions	Min.	Тур.	Max.	Units
Aging		Using Internal Reference	-	1	-	ppm/yr
Perference In Frequency		-	-	10	-	MHz
Reference In	Power	-	-3.5	-	+7.5	dBm
Frequency		-	-	10	-	MHz
Reference Out	Freq. Accuracy	Using Internal Reference	-	±1	-	ppm
	Power	-	-	+7	-	dBm
	Aging	Using Internal Reference	-	1	-	ppm/yr
Trigger Out, Low		-	0	-	0.4	
Trigger Out, High		-	2.4	-	3.3	V
Trigger In, Low		-	0	-	0.8	7 v
Trigger In, High		-	2.4	-	3.3	
Supply Voltage 8		-	- 22.8 24 25.2 V		V <sub>DC</sub>	
Supply Current <sup>8</sup>		-	-	400	500	mA
USB current 8						

<sup>&</sup>lt;sup>8</sup> Power On Sequence: Connect the 24V power, followed by the USB control before turning on the Generator

#### **Minimum System Requirements**

Interface	USB HID
Host operating system - USB Control	Windows 32/64 Bit operating system: Windows 98 <sup>®</sup> , Windows XP <sup>®</sup> , Windows Vista <sup>®</sup> , Windows 7 <sup>®</sup> , Windows 8, <sup>®</sup> , Windows 10, <sup>®</sup> Linux <sup>®</sup> support: 32/64 Bit operating system
Hardware	Pentium <sup>®</sup> II or better

#### **Absolute Maximum Ratings**

Operating Temperature	0ºC to +50ºC
Storage Temperature	-20°C to +60°C
Power in @ Reference In	+10 dBm
Reverse Power(DC) @ Reference Out	25V <sub>DC</sub>
Reverse Power(DC) @ RF Out	10V <sub>DC</sub>
Voltage @ Trigger out	-0.3V <sub>DC</sub> to +3.5V <sub>DC</sub>
Voltage @ Trigger in	-0.3V <sub>DC</sub> to +3.5V <sub>DC</sub>

Permanent damage may occur if any of these limits are exceeded.


#### Connections


RF Output	(N Type-Female)
Ref. In	(BNC-Female)
Ref. Out	(BNC-Female)
Trigger In	(BNC-Female)
Trigger Out	(BNC-Female)
Power In	(2.1 mm DC socket)
USB Port	(USB B female)


<sup>7</sup> Max trigger frequency is 200 kHz


#### **Typical Performance Curves\***


\*at +25°C unless mentioned otherwise


















#### Typical Performance Curves\* (continued)


\*at +25°C unless mentioned otherwise















#### Typical Performance Curves\* (continued)

\*at +25°C unless mentioned otherwise











#### Pulse mode definitions



#### **Outline Drawing LV1754**



# FRONT VIEW BACK VIEW SSG - 4000 HP 250 - 4000 MHz SYNTHESIZED SIGNAL GENERATOR RF OUTPUT SOQ POWER POWER POWER REF REF TRIG TRIG USB +224 VDC

#### Outline Dimensions (inch )

D

..... Mini-Circuits°

Α	В	С	D	E	F	G	Н	J	К	L	М	N	Р	WT. GRAMS
8.37	8.50	2.15	0.28	0.60	0.75	5.74	1.50	0.18	5.240	0.158	0.25	0.850	0.40	1000
212.6	215.9	54.6	7.1	15.2	19.05	145.8	38.1	4.6	133.1	4.0	6.35	21.6	10.2	1900

#### Ordering, Pricing & Availability Information see our web site

Model	Description					
SSG-4000HP	USB Synthesized Signal Generator					
Included Accessories	Part No.	Description				
	AC/DC-24-3W1	AC/DC 24V <sub>DC</sub> Grounded Power Adaptor. Operating temperature: 0°C to +40°C, I <sub>Max</sub> =2.5A				
	CBL-3W1-XX	AC Power Cord (Select one power cord from below with each Signal Generator)				
	SSG-CD	Software CD				
	USB-CBL-AB-3+	2.7 ft (0.8 m) USB Cable: USB type A(Male) to USB type B(Male)				

AC Power Cords <sup>9</sup>	Part No.	Description
	CBL-3W1-US	Power Cord for United States
4	CBL-3W1-EU	Power Cord for Europe
4	CBL-3W1-UK	Power Cord for United Kingdom
3	CBL-3W1-AU	Power Cord for Australia and China
-	CBL-3W1-IL	Power Cord for Israel

<sup>9.</sup> Power cords for other countries are also available, if you need a power cord for a country not listed in the table please contact apps@minicircuits.com or check http://www.minicircuits.com/contact/offices.html for regional offices e-mail and phone numbers.

<b>Optional Accessories</b>	Description	
USB-CBL-AB-3+ (spare)	2.7 ft. (0.8 m) USB cable	
USB-CBL-AB-7+	6.8 ft. (2.1 m) USB Cable	
USB-CBL-AB-11+	11 ft. (3.4 m) USB Cable	
BKT-280-07+	Bracket (One set of 2 each)	
Calibration	Description	
CALSSG-4000HP	Calibration Service	Click Here

#### **Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms");
  Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <a href="https://www.minicircuits.com/MCLStore/terms.jsp">www.minicircuits.com/MCLStore/terms.jsp</a>

