

Non-Catalog Model

RF Transformer

Impedance Ratio: 16:1

T16-1T+
T16-1T



CASE STYLE: W38

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.

Please click "Back", and then click "Contact Us" for Applications support.

+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

ELECTRICAL SPECIFICATIONS 50Ω @+25°C PIN=0 dBm


Parameter		Min.	Typ.	Max.	Units
Frequency		0.3		120	MHz
Insertion Loss*	3dB bandwidth	0.3		120	MHz
	2dB bandwidth	0.7		80	MHz
	1dB bandwidth	5		20	MHz

*Referenced to midband loss .9dB typ.

MAXIMUM RATINGS

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	250mW
DC Current	30mA

Configuration A



PIN CONNECTIONS

PRIMARY DOT	4
PRIMARY	6
SECONDARY DOT	3
SECONDARY	1
SECONDARY CT	2
NOT USED	5

 **Mini-Circuits**[®]
ISO 9001 ISO 14001 CERTIFIED

 **minicircuits.com**

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV. OR
M114099
T16-1T
080228