Surface Mount **RF** Transformer

0.07 to 200 MHz

T2-613-1+ T2-613-1



Generic photo used for illustration purposes only CASE STYLE: W38

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mA
Permanent damage may occur if any	of these limits are exceeded

Pin Connections

PRIMARY DOT	X1,Y5,Z3		
PRIMARY	X2,Y6,Z4		

Features

- wideband, 0.07 to 200 MHz
- single ended to balanced with impedance ratio selection
- also available with surface mount gull wing (KK81) plug-in (X65) leads

Applications


- HF/VHF
- test equipment

Transformer Electrical Specifications


Ω RATIO	FREQUENCY (MHz)	INSERTION LOSS*		
		3 dB MHz	2 dB MHz	1 dB MHz
1:1:2	0.07-200	0.07-200	0.1-100	0.5-50

^{*} Insertion Loss is referenced to mid-band loss, 0.4 dB typ.

Outline Drawing



NOTE: PIN NUMBERS DO NOT APPEAR ON UNIT, FOR REFERENCE ONLY. INDEX MARK NEAR PIN 6.




Outline Dimensions (inch)

E . 042 1.07	D . 010 0.25	C . 23 5.84	B . 27 6.86	A . 30 7.62
.036	.31	J .09	.05	G .100
	.042 1.07 L .036	.010 .042 0.25 1.07 K L .31 .036	.23 .010 .042 5.84 0.25 1.07 J K L .09 .31 .036	.27 .23 .010 .042 6.86 5.84 0.25 1.07 H J K L


Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
0.07	1.48	8.88	
0.20	1.34	15.76	
0.63	0.68	20.56	
2.00	0.47	25.22	
9.20	0.42	27.19	
29.09	0.49	23.67	
63.25	0.58	18.52	
100.24	0.77	15.39	
149.06	1.06	13.44	
200.00	1.45	13.77	

Config. F







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins.

 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively: "Standard Terms"): Purchases of this part. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

 The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp