Surface Mount **RF Transformer**

50Ω

0.2 to 350 MHz

Maximum Ratings

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mA
Permanent damage may occur if any	of these limits are exceeded.

Pin Connections

H

A .30

7.62

к

.020

TYF

С

.23 .010

М

.26 .575

6.60 14.61

в

.27

L

PRI

.036

0.91

6.86 5.84

PRIMARY DOT	4
PRIMARY	6
SECONDARY DOT	3
SECONDARY	1
SECONDARY CT	2
NOT USED	5

Outline Drawing

Outline Dimensions (inch)

Е

.042

1.07 0.51

Р

.600

15.24

Config. A

.

 \cap

D

Ν

0.25

NUMBERS DO NOT NOTE: PIN NUMBERS DO NOT APPEAR ON UNIT, FOR REFERENCE ONLY INDEX MARK INDICATES PIN 6.

TYP

F

Q

.125

3.18

.020

R TYP O TYP

SUGGESTED LAYOUT

G

R s

.050

.100

2.54

н

.05

1.27

.100 grams

2.54

J

.05

wt

0.50

1.27

S TYP

Features

- wideband, 0.2 to 350 MHz
- good return loss
- also available with flat-pack (W38), plug-in (X65) leads

Applications

- impedance matching
- receivers/transmitters
- balance antennas





Generic photo used for illustration purposes only CASE STYLE: KK81

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Transformer Electrical Specifications

Ω RATIO (Secondary/Primary)	FREQUENCY (MHz)	INSERTION LOSS*		
		3 dB MHz	2 dB MHz	1 dB MHz
4	0.2-350	0.2-350	0.35-300	2-100

*Insertion Loss is referenced to mid-band loss, 0.6 dB typ.

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
0.20	2.06	3.31	
0.35	1.33	7.01	
0.50	1.13	9.36	
1.00	0.92	12.67	
2.00	0.72	15.24	
5.00	0.59	17.34	
100.00	0.73	15.07	
175.10	0.91	12.93	
300.00	1.23	12.36	
350.00	1.34	13.08	



A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively: "Standard Terms"): Purphasers of this part Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable stabilished test performance data contained in this specification document are based on Mini-Circuit's applicable stabilished test performance data contained in this specification document are based on Mini-Circuit's applicable stabilished test performance data contained in this specification document are based on Mini-Circuit's applicable stabilished test performance data contained in this specification document are based on Mini-Circuit's applicable stabilished test performance data contained in this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's vebsite at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com