Surface Mount NON-CATA

50Ω

0.01 to 250 MHz


Maximum Ratings

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	250mW
DC Current	30mA
Permanent damage may occur if any	of these limits are exceeded

Pin Connections

4
6
3
1
_
2,5

Outline Drawing



Outline Dimensions (inch)					
A	B	C	D	E	F
.30	.27	.23	.010	.042	. 020
7.62	6.86	5.84	0.25	1.07	0.51
G	H	J	K	L	wt
. 100	.05	.09	.31	.036	grams
2.54	1.27	2.29	7.87	0.91	0.50

Config. C

Features

- wideband, 0.01 to 250 MHz
- excellent return loss
- also available with plug-in (X65) surface mount gull-wing (KK81) leads

Applications

- HF/VHF
- impedance matching



LOG_{T1.18-3+}

CASE STYLE: W38

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Transformer Electrical Specifications

Ω RATIO (Secondary/Primary)	FREQUENCY (MHz)	INSERTION LOSS*		
		3 dB MHz	2 dB MHz	1 dB MHz
1.18	0.01-250	0.01-250	0.02-200	0.03-50

* Insertion Loss is referenced to mid-band loss, 0.15 dB typ.

Typical Performance Data

·) prodi i orioritatioo 2 atta					
	FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)		
	0.01	1.28	9.92		
	0.04	0.30	19.95		
	0.10	0.20	26.49		
	0.13	0.25	21.52		
	0.40	0.16	31.57		
	5.04	0.14	28.04		
	74.29	0.86	11.69		
	128.74	1.30	6.88		
	169.30	1.42	4.22		
	250.00	1.62	1.40		



A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits

REV. C M151777 T1.18-3-KK81 IG/TD/CP/AM 160316