RF Transformer

 50Ω

0.03 to 20 MHz

T36-1-X65+ T36-1-X65



Generic photo used for illustration purposes only CASE STYLE: X65

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-20°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power	0.25W		
DC Current	30mA		
Pormonant damage may occur if any	of those limits are evenedo		

Pin Connections


4
6
3
1
2,5



Outline Dimensions (inch)

A	B	C	D	E	F	G
30	.27	. 23	. 010	. 042	. 020	.100
62	6.86	5.84	0.25	1.07	0.51	2.54
H 05 27	J .04 1.02	K .11 2.79	L .300 7.62	M .35 8.89	0.01	wt grams 0.50

Config. C



Features

- good return loss
- also available with flat-pack (W38) & surface mount gull-wing (KK81) leads

Applications

- amateur radio
- impedance matching


Transformer Electrical Specifications


Ω RATIO (Secondary/Primary)	FREQUENCY (MHz)	INSERTION LOSS*		
		3 dB MHz	2 dB MHz	1 dB MHz
36	0.03-20	0.03-20	0.05-10	0.1-5

^{*}Insertion Loss is referenced to mid-band loss, 0.4 dB typ.

Typical Performance Data

FREQUE((MHz)		N INPUT R. LOSS (dB)	
0.03	2.44	6.98	
0.05	1.60	9.75	
0.05	1.50	10.28	
0.10	0.89	15.22	
0.20	0.69	19.88	
0.27	0.67	20.32	
0.47	0.55	24.87	
2.17	0.38	16.92	
4.66	0.50	10.04	
20.00	2.58	1.81	





- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

 C. The parts covered by this specification document are subject to Mini-Circuit satandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp