## Non-Catalog Model

## **Frequency Mixer** Level 7 (LO Power +7 dBm)

## **Important Note**

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.

Please click "Back", and then click "Contact Us" for Applications support.



TAK-5R

CASE STYLE : A04

	ELECTRICA	L SPECIFICATION	NS 50Ω @ +25°	C	
Parameter		Min.	Тур.	Max.	Units
Frequency	LO (fL to fU)	0.05		200	MHz
	RF (fL to fU)	0.05		200	MHz
	IF	0		200	MHz
Conversion Loss	mid band		4.7	6.5	dB
	Total Range			8.0	dB
LO-RF Isolation	Low Range	50	55		dB
	Mid Range	35	45		dB
	Upper Range	35	45		dB
LO-IF Isolation	Low Range	45	50		dB
	Mid Range	30	40		dB
	Upper Range	30	40		dB
1 dB Comp. Input Power			+1		dBm

Notes: Low Range = [fL to 10fL] mid band = [2fL to fU/2] Mid Range = [10fL to fU/2]

Upper Range = [fU/2 to fU]


Hermatically sealed

MAXIMUM RATINGS		
Operating Temperature	-55°C to 100°C	
Storage Temperature	-55°C to 100°C	
RF Power	50mW	
IF Current	40mA	

PIN CONNECTIONS			
LO	8		
RF	1		
IF	3, 4 ^		
GROUND	2, 5, 6, 7		

^ - pins must be connected together externally

## **Electrical Schematics**





REV. X1 TAK-5R 060622 Page 1 of 1