# **RF Transformer**

#### 0.15 to 350 MHz 50Q

Generic photo used for illustration purposes only

#### CASE STYLE: AT224-1

#### Addition of Top hat™ feature

- · Allows faster pick-and-place · Enables visual identification marking
- +RoHS Compliant
  The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




# **Maximum Ratings**

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mA
Permanent damage may occur if any	of these limits are exceeded


## **Pin Connections**

PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	3
NOT USED	2

# Outline Drawing AT224-1



#### **PCB Land Pattern**




Suggested Layout, Tolerance to be within ±.002

### Outline Dimensions (inch)

<b>F</b>	<b>E</b>	<b>D</b>	C	<b>B</b>	<b>A</b>
. <b>025</b>	. <b>040</b>	. <b>050</b>	.160	. <b>150</b>	. <b>150</b>
0.64	1.02	1.27	4.06	3.81	3.81
grams	_	.030	J . <b>190</b> 4.83	H . <b>065</b>	G .028

#### Demo Board MCL P/N: TB-145 Suggested PCB Layout (PL-244)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS. 0.20" ± .0015"; COPPER: 1/2 0Z. ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE POB IS CONTINUOUS GROUND PLANE. 3. THIS PAD IS NOT REQUIRED FOR AT224 CASE STYLE. DENOTES POB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAYOUT WITH SMOBC SOLDER MASK OVER BARE COPPER)

#### • excellent amplitude unbalance, 0.1 dB typ. and phase unbalance, 2 deg typ. in 1 dB bandwidth plastic base with leads

• good return loss

• usable over 0.05-400 MHz

**Features** 

- **Applications** • balanced to unbalanced transformation
- push-pull amplifiers

## **Electrical Specifications**


$\Omega$ RATIO	FREQUENCY (MHz)	INSERTION LOSS*			
		3 dB MHz	2 dB MHz	1 dB MHz	
1	0.15-350	0.15-350	0.25-250	0.3-125	

\* Insertion Loss is referenced to mid-band loss, 0.2 dB tvp.

# Config. C CPRI SEC

## **Typical Performance Data**

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
0.15	0.73	12.89	
0.25	0.61	16.56	
0.30	0.57	17.77	
0.50	0.44	23.21	
2.00	0.31	30.49	
10.00	0.26	33.62	
50.00	0.35	24.13	
125.00	0.61	16.90	
250.00	1.31	11.59	
350.00	2.16	9.26	



- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

  B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

  C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp