

SURFACE MOUNT

RF Transformer

Mini-Circuits

50Ω 0.5 to 550 MHz

TC1.5-52T+

FEATURES

- Low insertion loss, 0.4 dB typ in 1 dB Bandwidth
- Excellent return loss, 25 dB typ. in 1 dB Bandwith
- Plastic base with leads
- Aqueous washable



Generic photo used for illustration purposes only CASE STYLE: AT224-1A

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- Impedance matching, 50 to 75 ohms
- Balanced amplifier

ELECTRICAL SPECIFICATIONS AT +25°C


Parameter	Frequency (MHz)	Min.	Тур.	Max.	Unit
Impedance Ratio (Secondary/Primary)			1.5		Ohm
Frequency Range		0.5		550	MHz
	0.5-550		3		
Insertion Loss*	1-350		2		dB
	2-200		1		

*Insertion Loss is referenced to mid-band loss, 0.4 dB typ.

MAXIMUM RATINGS

Parameter	Ratings		
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power	0.25 W		
DC Current	30 mA		

Permanent damage may occur if any of these limits are exceeded.







SURFACE MOUNT

⁻ Transformer

TC1.5-52T+

Mini-Circuits


500 0.5 to 550 MHz

PIN CONNECTIONS

Function	Pin Number
PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY CT	2
SECONDARY	3
NOT USED	5

PRODUCT MARKING: N/A

DEMO BOARD MCL P/N: TB-145 SUGGESTED PCB LAYOUT (PL-244)



1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


3. THIS PAD IS NOT REQUIRED FOR AT224 CASE STYLE.




DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern



Suggested Layout, Tolerance to be within±.002

OUTLINE DIMENSIONS (Inch)

F	E	D	C	B	A
. 025	.040	.050	.160	.150	. 150
0.64	1.02	1.27	4.06	3.81	3.81
wt		K	J	H	G
grams		.030	. 190	.065	.028
0.15		0.76	4.83	1.65	0.71

TAPE & REEL INFORMATION: F17

SURFACE MOUNT


RF Transformer

Mini-Circuits

50Ω 0.5 to 550 MHz

TYPICAL PERFORMANCE DATA

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)
0.50	0.82	15.72
1.00	0.61	19.84
5.00	0.33	28.81
10.00	0.29	32.35
50.00	0.35	28.60
100.00	0.41	23.52
200.00	0.53	18.07
250.00	0.61	16.13
300.00	0.70	14.71
400.00	0.90	12.52
550.00	1.28	10.19



NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and remedies thereinder, places with Mini Circuits' website at www.minisiers.utt.com/terms/viewterm.html

and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html