



SURFACE MOUNT


# RF Transformer

**TC4-1WA+**

50Ω 3 to 800 MHz

## FEATURES

- Wideband, 3 to 800 MHz
- Good Return Loss
- Plastic Base with Leads
- Aqueous Washable



Generic photo used for illustration purposes only

CASE STYLE: AT224-1A

### +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## APPLICATIONS

- Push-Pull Amplifier
- Impedance Matching

## ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Impedance Ratio			4		Ohms
Frequency Range		3		800	MHz
Insertion Loss <sup>1</sup>	3-800		3		dB
	5-400		2		dB
	10-100		1		dB


1. Insertion Loss is referenced to mid-band loss, 0.8 dB typ.

## ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-20°C to +85°C
Storage Temperature	-55°C to +100°C
RF Power	0.25 W
DC Current	30 mA

Permanent damage may occur if any of these limits are exceeded.

## CONFIG. A



REV. D  
ECO-025349  
TC4-1WA+  
MCL NY  
250428





**SURFACE MOUNT**

# RF Transformer

**TC4-1WA+**

Mini-Circuits

50Ω 3 to 800 MHz


## PIN CONNECTIONS

Function	Pin Number
PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	3
SECONDARY CT	2


**PRODUCT MARKING:** N/A

**DEMOBOARD MCL P/N:** TB-TC4-1WA+

## OUTLINE DRAWING



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

## OUTLINE DIMENSIONS (Inch mm)

A	B	C	D	E	F
.150	.150	.160	.050	.040	.025
3.81	3.81	4.06	1.27	1.02	0.64
G	H	J	K	wt	
.028	.065	.190	.030	grams	
0.71	1.65	4.83	0.76	0.15	

**TAPE & REEL INFORMATION: F17**



SURFACE MOUNT



# RF Transformer

TC4-1WA+

50Ω 3 to 800 MHz

## TYPICAL PERFORMANCE DATA

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)
3.00	1.09	11.58
4.00	0.98	12.35
5.00	0.93	13.11
7.50	0.86	14.21
10.00	0.83	14.49
100.00	0.88	15.77
250.00	0.96	16.17
400.00	1.13	16.72
600.00	1.36	15.59
800.00	2.21	9.07



### NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)

