RF Transformer

TC4-1W-7A+

50Q

125 to 135 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mA
Permanent damage may occur if any o	f these limits are exceeded

Pin Connections

PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	3
SECONDARY CT	2
NOT USED	5

Outline Drawing AT224-1



PCB Land Pattern




Suggested Layout, Tolerance to be within ±.002

Outline Dimensions (inch)

Α	В	С	D	E	F
.150	.150	.160	.050	.040	.025
3.81	3.81	4.06	1.27	1.02	0.64
G	н	1	K		wt
G .028	H .065	J .190	K .030	L .007	wt grams

Config. A



- · good return loss
- impedance matching
- plastic base with leads

- aqueous washable

Features

CASE STYLE: AT224-1

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Applications


catv

Transformer Electrical Specifications

Ω	FREQUENCY		INSERTION LOSS		
RATIO (Secondary/Primary)	(MHz)	3 dB MHz	2 dB MHz	1 dB MHz	
4	125-135	_	_	125-135	

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
100.0	0.36	28.39	
105.0	0.36	27.96	
110.0	0.37	27.54	
120.0	0.38	26.68	
125.0	0.38	26.26	
130.0	0.38	25.83	
135.0	0.39	25.40	
140.0	0.39	24.97	
145.0	0.40	24.55	
150.0	0.40	24.12	





A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp