

50 Ω Wideband 20 to 2500 MHz

TCBT-2R5GL+



CASE STYLE: GU1840

The Big Deal

•Wideband, 20 to 2500 MHz

- •Very low insertion loss, 0.4 dB
- •Excellent VSWR, 1.05:1
- •Tiny size, 0.15 x 0.15 x 0.14"

Product Overview

Mini-Circuits' TCBT-2R5GL+ is an ultra-wideband surface-mount bias tee covering applications from 20 to 2500 MHz with low insertion loss, excellent VSWR, and high DC-RF isolation over its entire frequency range. This model is capable of handling up to +30 dBm (1W) RF input power and DC input current up to 200mA. The unit features core and wire construction mounted on a ceramic base (0.15 x 0.15 x 0.14") with Mini-Circuits Top-Hat feature for faster, more accurate pick and place assembly.

Key Features

Feature	Advantages
Wideband, 20 to 2500 MHz	Supports a wide range of applications with a single device, including biasing broadband amplifiers, laser diodes, active anten- nas and more.
Low insertion loss, 0.4 dB	Preserves signal strength from input to output and minimizes overall system loss
Excellent VSWR, 1.05:1	Provides excellent matching for 50 Ω systems with minimal signal reflection.
RF power handling up to 1W	This model supports applications with a variety of power requirements.
Excellent DC-RF isolation	High DC-RF isolation (44 dB typ. at midband) minimizes RF leakage and interference with other elements in the system.
Miniature size, 0.15 x 0.15 x 0.14"	Small footprint makes the TCBT-2R5GL+ a space-saver in dense PCB-layouts.
Top-Hat feature	Improves speed and accuracy of pick and place assembly.
Leads for excellent solderability.	This model features leads to facilitate soldering on PCB assemblies.



Features

- wideband, 20 to 2500 MHz
- low insertion loss, 0.4 dB typ.
- miniature surface mount 0.15"x0.15"
- aqueous washable
- protected by US Patent 7,012,486

Applications

- biasing amplifiers
- · biasing of laser diodes
- biasing of active antennas

Electrical Specifications						
Parameter	Frequency (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range		20		2500	MHz	
	20-200		0.2	0.8		
Insertion Loss	200-1250	-	0.35	0.8	dB	
	1250-2500		0.7	1.2		
	20-200	40	65			
Isolation	200-1250	25	44	—	dB	
	1250-2500	20	40	-		
	20-200		1.05	1.5		
VSWR	200-1250		1.05	1.2	:1	
	1250-2500		1.1	1.25		
DC Resistance, DC to RF and DC port		-	0.2	-	ohms	

Maximum Ratings

Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	30 dBm max.
Voltage at DC port	25 V max.
DC Current	200mA

Permanent damage may occur if any of these limits are exceeded.


Product Marking



Pad Terminations

Function	Pad Number
RF	4
RF&DC	3
DC	1
ISOLATE (see PCB Layout)	2

Functional Schematic





TCBT-2R5GL+




Generic photo used for illustration purposes only

CASE STYLE: GU1840


+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

	Available Tape and Reel at no extra cost
Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500, 1000
13"	2000

TCBT-2R5GL+




PCB Land Pattern



Outline Dimensions (inch)

А	В	С	D	Е	F
.166	.150	.155	.100	.037	.025
4.22	3.81	3.94	2.54	0.94	0.64
G	н	J	к	L	wt
G .012	H .060	J .184	K .030	L 0.004	wt grams



Typical Performance Data

Frequency (MHz)	INSERTION LOSS (dB)	VSWR (:1)			lation mA
		RF	RF&DC	RF-DC	RF&DC-DC
20.00	0.26	1.13	1.11	59.24	58.93
50.00	0.24	1.05	1.04	59.60	75.37
100.00	0.22	1.02	1.02	69.83	72.61
500.00	0.28	1.02	1.01	51.83	51.15
1000.00	0.43	1.04	1.04	40.89	38.59
1500.00	0.64	1.06	1.08	35.46	31.24
2000.00	0.72	1.04	1.11	33.88	26.97
2200.00	0.74	1.04	1.13	33.78	25.75
2400.00	0.75	1.03	1.14	33.55	24.74
2500.00	0.75	1.03	1.14	33.30	24.28

