RF Transformer

TC9-1-75G2+

 75Ω

0.3 to 475 MHz


Maximum Ratings

Operating Temperature	-20°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power	0.25W		
DC Current	30mA		
Dormanant damaga may assur if any	of those limits are avecaded		


Pin Connections

PRIMARY DOT	6
PRIMARY	3
SECONDARY DOT	1
SECONDARY	3

Outline Drawing AT224-3



PCB Land Pattern




Suggested Layout, Tolerance to be within ±002

Outline Dimensions (inch)

F	Е	D	С	В	Α
.025	.030	.050	.150	.150	.150
0.64	0.76	1.27	3.81	3.81	3.81
wt		K	J	Н	G
grams		.030	.190	.065	.028
0.10		0.76	4.83	1.65	0.71

Demo Board MCL P/N: TB-276



Features

- suitable for tin/lead and RoHS solder systems
- wideband, 0.3 to 475 MHz
- good return loss, 23 dB typ. in 1 dB bandwidth
- step-down 9:1 autotransformer
- aqueous washable

Applications

matching laser diode



CASE STYLE: AT224-3

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Transformer Electrical Specifications


Ω RATIO (Primary/Secondary)	FREQUENCY (MHz)	INSERTION LOSS*		
		MHz	MHz	MHz
75/8	0.3-475	0.3-475	0.5-450	0.9-370

Insertion Loss is referenced to mid-band loss, 0.4 dB tvp. Stepdown, 75 ohm primary, 51 pF across secondary

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
0.30 0.50 0.90 10.00 100.00 200.00 300.00 370.00 450.00 475.00	0.80 0.71 0.66 0.36 0.44 0.42 0.29 0.29 0.84 1.40	14.70 16.80 18.13 22.63 22.86 22.40 23.48 18.53 9.48 7.44	





- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp