# Surface Mount $\mathbf{I}^{\text{top hat}}$ **RF Transformer** 75 $\Omega$ 0.3 to 475 MHz

## Features

- wideband 0.3-475 MHz
- good return loss, 23 dB typ in 1 dB bandwidth
- step-down 9:1 autotransformer
- plastic base with leads
- aqueous washable

# Applications

• matching laser diode





Generic photo used for illustration purposes only

CASE STYLE: AT1521

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

	Available Tape and Reel at no extra cost
Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500
13"	1000, 2000

#### **Electrical Specifications at 25°C**

Parameter	Condition	Min.	Тур.	Max.	Unit
Impedance Ratio (secondary / primary)			75/8		Ohm
Frequency Range		0.3		475	MHz
	0.3-475		3.0		
Insertion Loss*	0.5-450		2.0		dB
	0.9-370		1.0		

\* Insertion Loss is referenced to mid-band loss, 0.4 dB typ.

Stepdown, 75 ohm primary, 51 pF across secondary

#### **Maximum Ratings**

Parameter	Ratings		
Operating Temperature	-20°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power	0.25W		
DC Current	30mA		

Permanent damage may occur if any of these limits are exceeded.


**Product Marking** 

### **Pin Connections**

Pin Number				
6				
3				
1				
3				

Demo Board MCL P/N: TB-276








www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

# TC9-1-75X+


#### **Outline Drawing**



·	• • • • • • • •					
	F	E	D	С	В	Α
	.025	.040	.050	.160	.150	.150
	0.64	1.02	1.27	4.06	3.81	3.81
	wt		к	J	н	G
	grams		.030	.190	.065	.028
	0.15		0.76	4.83	1.65	0.71

#### **Typical Performance Data**

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
0.30	0.80	14.70	
0.50	0.71	16.80	
0.90	0.66	18.13	
10.00	0.36	22.63	
100.00	0.44	22.86	
200.00	0.42	22.40	
300.00	0.29	23.48	
370.00	0.29	18.53	
450.00	0.84	9.48	
475.00	1.40	7.44	



#### **Additional Notes**

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

