# Surface Mount **RF Transformer** 50Ω 20 to 4000 MHz

#### **Features**

- wide bandwidth 20 to 4000 MHz
- balanced transmission line
- good return loss
- aqueous washable

# Applications

- PCS
- wideband push-pull amplifiers
- cellular





Generic photo used for illustration purposes only

CASE STYLE: DB1627

#### +RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

	Available Tape and Reel at no extra cost
Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500
13"	1000, 2000

# Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Тур.	Max.	Unit
Impedance Ratio (secondary/primary)			2		
Frequency Range		20	_	4000	MHz
Insertion Loss	20 - 4000	—	1.5	2.5	dB
Amplitude Unbalance	20 - 4000	—	0.5	_	dB
Phase Unbalance	20 - 4000	_	10	—	Degree

#### **Electrical Schematic**



#### **Maximum Ratings**

Parameter	Ratings		
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power	0.4W		
DC Current	30mA		

Permanent damage may occur if any of these limits are exceeded.


# Product Marking



### **Pin Connections**


Function	Pin Number		
PRIMARY DOT	3		
PRIMARY	2		
SECONDARY DOT	4		
SECONDARY	6		
GND	2,5		
NOT USED	1		





# TCM3-452X-1+

# **Outline Drawing**




# Outline Dimensions (inch )

F	E	D	С	В	Α
.025	.040	.050	.160	.150	.160
0.64	1.02	1.27	4.06	3.81	4.06
wt		к	J	н	G
grams		.030	.190	.065	.028
0.15		0.76	4.83	1.65	0.71

### **Typical Performance Data**


Frequency (MHz)	Insertion Loss (dB)	Input R. Loss (dB)	Amplitude Unbalance (dB)	Phase Unbalance (Deg.)
20.0	1.75	8.54	0.09	5.03
100.0	1.85	8.85	0.79	0.68
500.0	1.63	9.05	0.21	5.63
1100.0	1.50	10.61	0.36	8.44
1500.0	1.42	12.35	0.24	9.42
1900.0	1.36	14.90	0.02	10.43
2100.0	1.34	16.71	0.17	10.77
2500.0	1.32	21.96	0.34	10.82
3100.0	1.34	22.72	0.55	10.36
4000.0	1.57	12.43	0.45	2.13


\* Note: 0.25 PF capacitor is suggested to be added at primary to ground to improve return loss.



1500 2000 2500 3000 3500 4000

FREQUENCY (MHz)





#### Additional Notes

1.0

0.5

0.0 0 500 1000

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are www.minicircuits.com/MCLStore/terms.jsp