RF Transformer

TCM4-14



CASE STYLE: DB714
PRICE: Contact Sales Dept.

50Ω 200 to 1400 MHz

Maximum Ratings


Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mA

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	3
SECONDARY	1
SECONDARY CT	2
NOT USED	5

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch)

A .160	B .150	C .160	D .050	E .040	F .025
4.06	3.81	4.06	1.27	1.02	0.64
G	Н	J	K		wt
.028	.065	.190	.030		grams
0.71	1.65	4.83	0.76		0.15

Config. A



Features

- wide bandwidth, 200 to 1400 MHz
- good return loss
- plastic base with solder plated leads
- aqueous washable

Applications

• impedance matching


Transformer Electrical Specifications


Ω RATIO (Secondary/Primary)	FREQUENCY (MHz)	3 dB MHz	INSERTION LOSS* 2 dB MHz	1 dB MHz
4	200-1400	200-1400	300-1300	800-1000

^{*} Insertion Loss is referenced to mid-band loss, 0.8 dB typ.

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
200.00	1.22	11.75	
300.00	1.11	13.94	
500.00	0.85	17.09	
700.00	0.86	18.47	
800.00	0.76	16.98	
1000.00	0.67	12.08	
1200.00	0.69	8.13	
1300.00	0.90	6.67	
1350.00	1.06	6.06	
1400.00	1.35	5.52	
	200.00 300.00 500.00 700.00 800.00 1000.00 1200.00 1300.00 1350.00	(MHz) LOSS (dB) 200.00 1.22 300.00 1.11 500.00 0.85 700.00 0.86 800.00 0.76 1000.00 0.67 1200.00 0.69 1300.00 0.90 1350.00 1.06	(MHz) LOSS (dB) R. LOSS (dB) 200.00 1.22 11.75 300.00 1.11 13.94 500.00 0.85 17.09 700.00 0.86 18.47 800.00 0.76 16.98 1000.00 0.67 12.08 1200.00 0.69 8.13 1300.00 0.90 6.67 1350.00 1.06 6.06





Mini-Circuits

ISO 9001 ISO 14001 AS 9100 CERTIFIED

For detailed performance specs

