

Non-Catalog Model

Frequency Mixer

TFM-2LH

Level 10 (LO Power +10 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : B02

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	2		1000	MHz
	RF (fL to fU)	2		1000	MHz
	IF	0		1000	MHz
Conversion Loss	mid band		5.7	7.5	dB
	Total Range			9.2	dB
LO-RF Isolation	Low Range	45	62		dB
	Mid Range	25	44		dB
	Upper Range	25	37		dB
LO-IF Isolation	Low Range	40	58		dB
	Mid Range	25	45		dB
	Upper Range	18	31		dB
1 dB Comp. Input Power			+5		dBm

Notes: Low Range = [fL to 10fL]
mid band = [2fL to fU/2]

Mid Range = [10fL to fU/2]

Upper Range = [fU/2 to fU]

Hermetically sealed

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	4
RF	1
IF	2
GROUND	3

Electrical Schematics

