Surface Mount **RF Transformer** 800 to 1900 MHz

50Ω

Features

- wideband, 800 to 1900 MHz
- balanced transmission line
- plastic base with solder plated leads • aqueous washable

Applications

- cellularPCN
- GPS
- baluns
- impedance matching





Generic photo used for illustration purposes only

CASE STYLE: DB714

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

	Available Tape and Reel at no extra cost
Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500
13"	1000, 2000

Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Тур.	Max.	Unit
Impedance Ratio			1		Ohm
Frequency Range		800		1900	MHz
Insertion Loss*	800 - 1900		3		dB
	800 - 1400		1		

* Insertion Loss is referenced to mid-band loss, 0.2 dB typ.

Maximum Ratings

Parameter	Ratings
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mA

Permanent damage may occur if any of these limits are exceeded.

Pin Connections


Function	Pin Number
PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	3
NOT USED	2,5

Config. G



TCML1-19+


Outline Drawing



Outline Dimensions (inch)

А	В	С	D	E	F
.160	.150	.160	.050	.040	.025
4.06	3.81	4.06	1.27	1.02	0.64
G	н	J	К		wt
.028	.065	.190	.030		grams
			.000		9.4

Demo Board MCL P/N: TB-145+ Suggested PCB Layout (PL-244)



DENOTES COPPER LAND PÁTTERN FREE OF SOLDER MASK


Typical Performance Data

🗕 D TYP

H TYP

-K TYP

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)
800.00	0.30	11.91
850.00	0.59	12.02
900.00	0.31	12.44
1000.00	0.39	13.40
1200.00	0.14	17.22
1400.00	0.13	20.13
1500.00	0.14	16.01
1600.00	0.34	12.26
1700.00	0.55	9.49
1900.00	1.22	5.94



Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are www.minicircuits.com/MCLStore/terrs.jsp