Frequency Mixer

TUF-860SM

Level 7 (LO Power +7 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE: NNN150

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C						
Parameter		Min.	Тур.	Max.	Units	
Frequency	LO (fL to fU)	800		1050	MHz	
	RF (fL to fU)	800		1050	MHz	
	IF	0		250	MHz	
Conversion Loss			5.6	7.8	dB	
LO-RF Isolation		25	35		dB	
LO-IF Isolation		20	27		dB	
1 dB Comp. Input Power			+1		dBm	

Note: Non-hermetic

MAXIMUM RATINGS			
Operating Temperature	-55°C to 100°C		
Storage Temperature	-55°C to 100°C		
RF Power	50mW		
IF Current	40mA		

PIN CONNECTIONS			
LO	4		
RF	1		
IF	2		
GROUND	3		

Electrical Schematics

