Coaxial Low Pass Filter

50Ω

*DC to 2250 MHz

Maximum Ratings

-		
Operating Temperature	-55°C to 100°C	
Storage Temperature	-55°C to 100°C	
RF Power Input*	10W max. at 25°C	
DC Current Input to Output	0.5A max. at 25°C	

* Passband rating, derate linearly to 3.5W at 100°C ambient. Permanent damage may occur if any of these limits are exce

Features

- rugged uni-body construction, small size
- 7 sections
- excellent power handling, 10W
- temperature stable
- low cost
- protected by U.S. Patent 6,943,646

Applications

- harmonic rejection
- transmitters/receivers
- · lab use





Generic photo used for illustration purposes only CASE STYLE: FF704 Connectors Model SMA VLF-2250(+)

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch)

В	D	E	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0

Electrical Specifications at 25°C PASSBAND STOP BAND (MHz) fco, MHz VSWR NO. OF SECTIONS (MHz) Nom. (loss, dB) (:1) (loss < 1.2 dB) (loss 3 dB) f 20 30 fr 20 Stopband Passband Max Тур. Min Тур Тур Тур. Тур *DC-2200 2575 3000-5000 7200 20 1.2 7 2900

Not for use with DC voltage at input and output ports

typical frequency response



electrical	schematic	



Typical Performance Data at 25°C

Frequen	су	Insertion Loss	VSWR	
(MHz)		(dB)	(:1)	
50.00		0.06	1.01	
500.00		0.11	1.02	
1000.00		0.15	1.05	
1500.00		0.33	1.07	
2000.00		0.51	1.06	
2250.00		0.82	1.20	
2575.00		2.84	2.10	
2850.00		24.55	7.08	
3800.00		48.40	32.18	
4250.00		37.39	34.07	
5000.00		33.16	36.97	
6500.00		37.38	30.49	
7200.00		30.64	39.49	
8000.00		7.60	9.69	
9000.00		14.79	30.49	

1000





VLF-2250

VSWR

Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV .I M151107 VLF-2250 EDR-6469/5 AD/TD/CP/AM 200522 Page 1 of 1