

High Pass Filter

Mini-Circuits

50Ω 2010 to 10100 MHz

XHF-23+

THE BIG DEAL

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent Power handling
- Temperature stable, up to 105°C
- Small size, 3 x 3 mm
- Protected by US Patent No. 8,392,495

APPLICATIONS

- Wi-Fi
- WiMax
- Microwave Radio
- Military & Space

GENERAL DESCRIPTION


Mini-Circuits' XHF-23+ reflectionless filter employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level. These reflections interact with neighboring components and often result in inter-modulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

KEY FEATURES

Feature	Advantages
Easy integration with sensitive reflective com- ponents, e.g. mixers, multipliers	Reflectionless filters absorb unwanted signals falling in filter stopband, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range and saving board space.
High stopband rejection, up to 50 dB	Ideal for applications where suppression of strong spurious signals and intermod- ulation products is needed.
Enables stable integration of wideband amplifiers	Because reflectionless filters maintain good impedance in the stopband; they can be integrated with high gain, wideband amplifiers without the risk of creating instabilities in these out of band regions.
Cascadable	Reflectionless filters can be cascaded in multiple sections to provide sharper and higher attenuation, while also preventing any standing waves that could affect passband signals. Low & highpass filters can be cascaded to realize bandpass filters.
Excellent power handling in a tiny surface mount device up to 7W in passband	High power handling extends the usability of these filters to the transmit path for inter-stage filtering.
Small size, 3x3mm QFN-Style	Allows replacement of filter/attenuator pairs with a single reflectionless filter, saving board space.
Excellent repeatability of RF performance	Through semiconductor IPD process, X-series filters are inherently repeatable for large volume production.
Operating temperature up to 105 °C	Suitable for operation close to high power components.

IPD - Integrated Passive Device, is a GaAs semiconductor process





Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant

ligh Pass Filter F



Mini-Circuits

50Ω 2010 to 10100 MHz

ELECTRICAL SPECIFICATIONS¹ AT +25°C

	Parameter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Rejection	DC-F1	DC-1210	12	14	—	dB
Stop Band	Frequency Cut-off	F2	1650	_	3.0	-	dB
	VSWR	DC - F1	DC-1210	_	1.2	-	:1
	Insertion Loss	F3-F5	2010 -10100	_	1.2	2.0	dB
Pass Band VSWR	F3-F4	2010 - 3200	_	1.6	_	:1	
	VSVVK	F4-F5	3200 - 10100	_	2.0	_	:1

1. Measured on Mini-Circuits Characterization Test Board TB-844-23H+


ABSOLUTE MAXIMUM RATINGS²

Parameter	Ratings	
Operating Temperature	-55°C to +105°C	
Storage Temperature	-65°C to +150°C	
RF Power Input, Passband (F3-F5) ³	2 W at +25°C	
RF Power Input, Stopband (DC-F3)⁴	0.5 W at +25°C	

2. Permanent damage may occur if any of these limits are exceeded.

Passband rating derates linearly to +1W at 105°C ambient
Stopband rating derates linearly to +0.25W at 105°C ambient

SPECIFICATION DEFINITION




High Pass Filter


XHF-23+

Mini-Circuits


50Ω 2010 to 10100 MHz

SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION





Function	Pad Number	Description
RF-IN	2	RF Input Pad
RF-OUT	8	RF Output Pad
GND	1,3,7,9, Paddle	Connected to ground
NC (GND Externally)	4,5,6,10,11,12	No internal connection



Marking may contain other features or characters for internal lot control

High Pass Filter




Mini-Circuits

50Ω 2010 to 10100 MHz

TYPICAL PERFORMANCE DATA AT +25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	37.56	1.08
20	35.92	1.08
50	31.08	1.06
100	25.62	1.08
200	20.18	1.09
400	15.49	1.13
800	16.17	1.20
1210	13.58	1.22
1650	2.78	1.13
2010	1.00	1.21
2500	0.51	1.38
2800	0.45	1.48
3200	0.46	1.60
4000	0.48	1.73
5000	0.41	1.65
6000	0.32	1.46
7000	0.28	1.34
8000	0.42	1.33
9000	0.17	1.41
10100	0.34	1.45



High Pass Filter

Mini-Circuits

50Ω

2010 to 10100 MHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS CLICK HERE

	Table
Performance Data & Graphs	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle lead finish: matte-tin
Tape & Reel Standard quantities available on reel	F66 7" reels with 20, 50, 100, 200, 500 ,1000, 2000 or 3000 devices devices
Suggested Layout for PCB Design	PL-451
Evaluation Board	TB-844-23H+ (without connectors) TB-844-23HC+ (with connectors) B20-118-F1+ Connector sold separately
Environmental Ratings	ENV82


ESD RATING

Human body model (HBM): Class 2 (2000 to < 4000 V) in accordance with ANSI/ESD 5.1-2001

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

MSL TEST FLOW CHART




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com PAG

High Pass Filter

Mini-Circuits

50Ω 2010 to 10100 MHz

REFLECTIONLESS FILTER APPLICATION NOTE






Figure 1. IF output reflection spectrum without filter




Figure 3. IF output reflection spectrum with reflectionless filter

A Perform

• Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Figure 2. IF output reflection spectrum with conventional filter

An application circuit was assembled to measure the IF reflection spectrum at the output of a mixer when the mixer was paired with a conventional filter versus a reflectionless filter.

While the conventional filter reduces the reflections present when the mixer is used alone (no filter), the reflectionless filter virtually eliminates those reflections altogether.

The reflected signal at marker 1 in the figures above exhibits a reduction of more than 20 dB from -28.7 dBm to -50.3 dBm when the reflectionless filter is used as compared to the conventional filter, thus eliminating unwanted spurious mixing products and improvingsystem dynamic range.

For more information, refer to application note AN-75-007

Mini-Circuits®