

Coaxial

Frequency Mixer

ZAD-11H

Level 17 (LO Power +17 dBm) 10 to 3000 MHz



CASE STYLE: M22

Connectors	Model
BNC	ZAD-11H
BRACKET (OPTION "BR")	

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

LO	1
RF	3
IF	2


Features

- low conversion loss, 6.83 dB typ.
- wideband, 10 to 3000 MHz
- rugged shielded case

Applications

- PCS/DCS
- cellular
- satellite distribution
- GPS
- instrumentation

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
2.25	1.38	1.24	.50	.150	3.100	.138	1.238
57.15	35.05	31.50	12.70	3.81	78.74	3.51	31.45

J	K	L	M	N	P	S	wt
3.25	.10	.40	1.15	1.86	.64	.150	grams
82.55	2.54	10.16	29.21	47.24	16.26	3.81	74.0

Electrical Specifications


FREQUENCY (MHz)	CONVERSION LOSS (dB)	LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)									
		LO/RF		IF		Mid-Band		Total Range		L		M		U			
f_1 - f_2	\bar{X} σ Max.	\bar{X} σ Max.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.			
10-3000	10-1000	6.83	0.09	10.0	12.0	27	20	25	18	23	16	27	20	25	18	23	16

1 dB COMP.: +10 dBm typ. L = low range [f_1 to $10 f_1$] M = mid range [$10 f_1$ to $f_1/2$] U = upper range [$f_1/2$ to f_1]
m = mid band [$2f_1$ to $f_1/2$]

Typical Performance Data

Frequency (MHz)	Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
10.00	40.00	6.43	32.26	1.13	2.07
20.00	50.00	6.58	33.52	1.07	2.19
103.44	73.44	6.60	32.25	1.08	2.01
200.00	170.00	6.78	30.89	1.13	1.96
290.31	260.31	6.75	29.76	1.18	1.91
500.00	470.00	6.94	28.74	1.29	1.83
570.63	540.69	6.81	28.80	1.34	1.81
757.50	727.50	7.00	28.06	1.48	1.81
944.38	913.91	7.05	28.00	1.66	1.80
1037.80	1007.40	7.37	28.67	1.72	1.74
1318.10	1288.00	6.81	27.69	1.92	1.69
1505.00	1474.90	6.68	27.57	1.99	1.65
1598.40	1568.30	6.65	27.30	1.75	1.91
1785.30	1755.00	6.71	27.75	1.89	1.91
1972.20	1942.10	6.57	29.51	1.76	1.75
2065.60	2035.10	6.76	28.94	1.68	1.66
2252.50	2222.10	6.61	30.22	1.68	1.49
2439.40	2408.60	6.63	31.19	1.69	1.14
2626.30	2596.00	6.95	30.21	1.49	1.26
3000.00	2969.30	8.58	32.46	1.90	2.47







Electrical Schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp





Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp