# SPDT RF Switch

Absorptive RF Switch with internal driver. Single Supply Voltage, +3V to +5V

#### **Product Features**

- High Isolation, 65 dB typ. at 1 GHz
- Low insertion loss, 1.0 dB typ. at 1 GHz
- High IP3, 50 dBm typ. at 1 GHz
- Fast switching, Rise/fall time, 23 ns typ.
- Low current consumption, 12 μA typ.

#### **Typical Applications**

- Automated switching networks
- Cellular/ PCS
- ISM, WCDMA, WiMAX, LTE

500-6000 MHz


VSWA2-63DR+ CASE STYLE: DG1235-1

50Ω

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## **General Description**

VSWA2-63DR+ is a high isolation absorptive SPDT switch with integral CMOS driver, operates with single positive supply voltage while consuming, 12µA typical. It has been designed for very wideband operation of 500-6000 MHz for 50 $\Omega$  systems and yet is usable in 75 $\Omega$  systems with degraded return loss. This switch is usable over an extended frequencies from 300 kHz to 500 MHz with reflective switch performance. It is packaged in a tiny 4mm x 4mm x 0.9mm package and is rated MSL1 and class 1A ESD.



#### Simplified Schematic and Pad Description

Function	Pad Number	Description
RF COM	3	RF Common/ SUM Port, requires DC block (see Fig. 2)
RF1	12	RF Out #1/In Port #1, requires DC block (see Fig. 2)
RF2	9	RF Out #1/In Port #2, requires DC block (see Fig. 2)
Control	2	CMOS Control IN
VDD	1	Supply Voltage
GND	4,5,6,7,8,10,11 13,14,15,16, paddle	RF Ground

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

ECO-018779 VSWA2-63DR+ ED-12806A MCL NY 230803 Page 1 of 5

## lMini-Circuits



#### **SPDT RF Switch**

## VSWA2-63DR+

Parameter	Condition (MHz)	Min.	Тур.	Max.	Units
Frequency Range		500		6000	MHz
	0.3 to 500		0.7		
	500 to 2000		0.7	1.3	
Insertion Loss <sup>(2)</sup>	2000 to 3000		0.8	1.5	dB
	3000 to 4000		0.9	1.5	UD UD
	4000 to 6000		1.0	1.9	
	0.3 to 500	—	73		
	500 to 2000	56	66		
Isolation between Common port and RF1/RF2 Ports	2000 to 3000	50	64		dB
	3000 to 4000	45	58		UD UD
	4000 to 6000	38	54		
	0.3 to 500		74		
	500 to 1000	50	60		
Isolation between RF1 and RF2 ports	1000 to 2000	45	56		
	2000 to 3000	40	52		dB
	3000 to 4000	38	50		
	4000 to 6000	34	46		
	0.3 to 500		24		
	500 to 2000		23		
Return Loss (ON STATE)	2000 to 3000		23		dB
	3000 to 4000		22		-
	4000 to 6000		20		
	500 to 2000		23		
Return Loss @ RF1/RF2 ports (OFF STATE)	2000 to 3000		33		dB
Retuin Loss @ RFI/RFZ poils (OFF STATE)	3000 to 4000		23		ub
	4000 to 6000		24		
Input IP3 V <sub>DD</sub> =3V	500 to 2000		46	İ	
	2000 to 6000		40		
V <sub>DD</sub> =5V	500 to 2000		50		dBm
	2000 to 6000		44		
Input Compression <sup>(3)</sup> 1dB,V <sub>DD</sub> =3V	500 to 2000		24		
	2000 to 6000		22		dDaa
0.2 dB, V <sub>DD</sub> =5V	500 to 2000		30		dBm
	2000 to 6000		27		

#### RF Electrical Specifications<sup>(1)</sup>, 500 - 6000 MHz, $T_{AMB}$ =25°C, $V_{DD}$ = +3V to +5V

#### **DC Electrical Specifications**

Parameter	Min.	Тур.	Max.	Units
VDD, Supply Voltage	3		5	V
Supply Current $(V_{DD} = 5V)^{(4)}$		50		μA
Control Voltage Low	0		0.5	V
Control Voltage High <sup>(5)</sup>	2.7(6)		V <sub>DD</sub>	V
Control Current		5		μA

Notes:

1. Tested on Mini-Circuit's test board TB-407+, using Agilent's N5230A network analyzer (see Characterization Test Circuit, Fig.1). 2. Insertion loss values are deembedded from test board loss.

3. Do not exceed RF input power as shown in Absolute Maximum Rating table.

Supply current increases with switching repetition rate. See graph.
CMOS interface. Latch up condition may occur when logic high signal is applied prior to power supply.

6. 3.5V for V<sub>DD</sub>=4 to 5V

#### **Switching Specifications**

Parameter	Min.	Тур.	Max.	Units
Rise/Fall Time (10 to 90% or 90 to 10% RF)		23		nSec
Switching Time, 50% CTRL to 90/10% RF		35		nSec
Video Feedthrough, (control 0 to 3V, freq.=500 KHz, V <sub>DD</sub> =5V)		25		mV <sub>P-P</sub>

Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"), Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



#### Absolute Maximum Ratings<sup>(6)</sup>

Parameter	Ratings	
Operating Temperature	-40°C to +85°C	
Storage Temperature	-65°C to 150°C	
V <sub>DD</sub> , Supply Voltage	2.7 to 5.5V	
Voltage Control	-0.2V Min. VDD Max.	
RF input power	1Watt	
Dissipated Power at 25°C	350mW	

6. Operation of this device above any of these conditions may cause permanent damage.

Truth Table	(State of control voltage selects the desired switch sta	ate)
-------------	--	------

State of Control Voltors	RF Common to		
State of Control Voltage	RF1	RF2	
Low	ON	OFF	
High	OFF	ON	

ON- low insertion loss state OFF- Isolation State

#### **Characterization Test Circuit**




Figure 1: Block Diagram Of Test Circuit Used For Characterization. (DUT soldered on Mini-Circuit's TB-407+)

#### **Test Equipment:**

For Insertion loss, Isolation, Return loss and DC current:

Agilent's N5230A Network Analyzer, E3631A power supply. Cblock: Internal to network Analyzer.

For Switching Time and DC Current: Agilent's 54832B oscilloscope, 81110A pulse generator and E3631 A power supply. Cblock: Mini-Circuits BLK-18-S+ For Input IP3:

Mini-Circuits DC blocks: BLK-18-S+ on all ports, Agilent's E8257D signal generators, 437B power meter,

N9020A Signal analyzer and E3631 A power supply.

For Compression:

Mini-Circuits DC blocks: BLK-18-S+ on all ports. ZVE-8G and ZHL-42W amplifier as driver amplifier at RF Common. Agilent's N5230A Network Analyzer, E3631A power supply

#### Conditions:

 $V_{pp}$  = +3 and +5V, Control= 0 and 3V.

For Insertion loss, isolation and return loss: Pin=0 dBm

For Input IP3: Pin=-5dBm/tone.


For Switching time: RF frequency: 500 MHz at 0 dBm, Control Frequency: 500 KHz and 0 and +3V.

Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

## -Circuits

### **Product Marking**





**Evaluation Board: TB-486+** 

**Environmental Ratings: ENV41** 

#### **Recommended Application Circuit**




Fig. 2: Evaluation board includes case, connectors and components soldered to PCB.

Frequency (MHz)	Cblock (Suggested value)
0.3-500	0.1µF
500-6000	47pF

Cblock should be free of resonance over frequency of operation.

#### Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp

## IMini-Circuits


### ESD Rating

Human Body Model (HBM): Class 1A (250 to < 500V) in accordance with JESD22-A114

Machine Model (MM): Class A (Passes 50V) in accordance with JESD22-A115

#### **MSL** Rating

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D



Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

## ni-Circuits