

Level 10 (LO Power +10 dBm) 3700 to 7000 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

LO	2
RF	1
IF	3

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G	H
1.00	.75	.58	.50	.29	.38	.140	--
25.40	19.05	14.73	12.70	7.37	9.65	3.56	--

J	K	L	M	N	P	wt
.687	--	.32	.13	.10	.16	grams
17.45	--	8.13	3.30	2.54	4.06	25.0

Features

- wide frequency range, 3700 to 7000 MHz
- low conversion loss, 5.4 dB typ.
- high L-I isolation, 35 dB typ.

Applications

- SATCOM
- instrumentation
- defense & federal communications
- SHF



CASE STYLE: BU413

Connectors	Model
SMA	ZMX-7GLHR

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS* (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)	
LO/RF	IF			Total Range Max.	Typ.	Min.	Typ.	Min.
$f_L - f_U$		$\bar{X}$	σ					
3700-7000	DC-1500	5.4	0.30	8.5	33	20	35	20


1 dB COMP: +5 dBm typ.

* Above 750 MHz IF, conversion loss increases up to 9.8 dB max.

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +10dBm	LO +10dBm	LO +10dBm	LO +10dBm	LO +10dBm
3700.00	3730.00	3.99	32.98	27.03	1.50	1.14
3886.79	3916.79	3.98	31.80	28.45	1.27	1.16
4000.00	4030.00	3.92	32.48	28.87	1.51	1.19
4198.11	4228.11	4.06	34.29	30.39	2.05	1.23
4384.91	4414.91	4.31	35.39	30.87	2.33	1.23
4571.70	4601.70	4.33	34.22	31.36	2.22	1.31
4758.49	4788.49	4.75	32.35	31.67	2.02	1.26
5000.00	4970.00	4.61	33.65	33.33	2.15	1.25
5194.34	5164.34	4.63	33.47	34.18	2.27	1.23
5381.13	5351.13	4.74	31.77	34.40	2.30	1.18
5567.92	5537.92	4.92	31.07	34.26	2.39	1.18
5754.72	5724.72	4.88	32.53	34.46	2.75	1.13
5941.51	5911.51	5.30	32.98	34.47	3.27	1.07
6000.00	5970.00	5.39	33.39	34.42	3.38	1.15
6190.57	6160.57	5.57	33.62	34.18	3.79	1.20
6377.36	6347.36	5.82	34.18	33.86	3.91	1.15
6564.15	6534.15	5.93	35.55	33.39	3.98	1.14
6750.94	6720.94	5.72	35.04	32.76	3.86	1.18
6937.74	6907.74	5.62	34.39	32.13	3.74	1.08
7000.00	6970.00	5.62	34.32	32.02	3.64	1.21







Electrical Schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp





Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp